



RoadFlair

BRP394 LED335/NW 280W DM MP1 ILT

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

Product data

General Information	
Light source color	740 neutral white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	Polycarbonate micro lens optic
Connection	Mains outlet socket
Cable	Cable 0.5 m without plug
Protection class IEC	Safety class I
CE mark	CE mark
Optic type outdoor	Medium beam
Constant light output	Programmable
Light source engine type	LED
Light Technical	
Standard tilt angle side entry	5°
Operating and Electrical	
Input Voltage	220-240 V
Input Frequency	50 or 60 Hz

Power Factor (Min)	0.95
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Mounting device	Side-entry for diameter 48 to 60 mm
Optical cover/lens shape	Ball, globular
Overall length	870 mm
Overall width	295 mm
Overall height	86 mm
Color	Gray

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]

RoadFlair

Mech. impact protection code	IK08 [5 J vandal-protected]
Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	33500 lm
Luminous flux tolerance	+/-5%
Initial LED luminaire efficacy	119.64285714285714 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	>70
Initial chromaticity	(0.433, 0.401) SDCM>5
Initial input power	280 W
Power consumption tolerance	+/-5%

Application Conditions


Ambient temperature range	-30 to +50 °C
---------------------------	---------------

Product Data

Full product code	911401600204
Order product name	BRP394 LED335/NW 280W DM MP1 ILT
Order code	911401600204
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911401600204
Net Weight (Piece)	9.999 kg



Dimensional drawing



BRP391/392/393/394 RoadFlair

