



FlowBase

BWP352 LED29/NW 25W 220-240V DM2 MP1

FlowBase, 2900 lm, 25 W, 740 neutral white, Wide beam, Safety class I, Wall-mounting bracket

A lighting design that ensures safety and good visibility is a key element in the success of any tunnel project. Philips FlowBase combines compact design, reliability, and affordability in one complete package to bring the perfect lighting solution for any tunnel application.

Product data

General Information		Cable	
Light source replaceable	No	Cable 0.45 m without plug	
Driver included	Yes	Temperature	
Light source engine type	LED	Ambient temperature range	
CE mark	CE mark	-40 to +50 °C	
Light Technical		Controls and Dimming	
Luminous Flux	2,900 lm	Dimmable	
Correlated Color Temperature (Nom)	4000 K	Constant light output	
Luminous Efficacy (rated) (Nom)	116 lm/W	No	
Color rendering index (CRI)	>70	Mechanical and Housing	
Light source color	740 neutral white	Housing Material	
Optic type outdoor	Wide beam	Aluminum die cast	
Operating and Electrical		Optic material	
Input Voltage	220-240 V	Polycarbonate	
Line Frequency	50 or 60 Hz	Optical cover material	
Power Consumption	25 W	Polycarbonate	
Power Factor (Fraction)	0.95	Housing Color	
		Grey	
		Mounting device	
		Wall-mounting bracket	
		Optical cover shape	
		Ball, globular	
		Overall length	
		429 mm	
		Overall width	
		150 mm	
		Overall height	
		122 mm	

Dimensions (Height x Width x Depth)	122 x 150 x 429 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-5%
Initial chromaticity	(0.433, 0.401) SDCM>5
Power consumption tolerance	+/-5%

Product Data	
Order product name	BWP352 LED29/NW 25W 220-240V DM2 MP1
Full product name	BWP352 LED29/NW 25W 220-240V DM2 MP1
Full product code	911401609103
Order code	911401609103
Material Nr. (12NC)	911401609103
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

