



## Tango G3 - BVP38x

## BVP381 LED130/CW 100W 220-240V SWB GM

Tango G3 - BVP38x, 13000 lm, 100 W, Cool white, Symmetrical wide beam,  $85^{\circ}$  x  $85^{\circ}$ , Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

## **Product data**

General Information	
Lamp family code	-
Light source replaceable	Yes
Number of gear units	-
Driver included	Yes
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	-
ENEC mark	-
EU RoHS compliant	No
Light Technical	
Luminous Flux	13,000 lm

Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	130 lm/W
Color rendering index (CRI)	70
Light source color	Cool white
Optical cover type	Polycarbonate micro lens optic
Luminaire light beam spread	85° x 85°
Optic type outdoor	Symmetrical wide beam
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W

Datasheet, 2023, December 5 data subject to change

## Tango G3 - BVP38x

End CLO power consumption	- W
Power Consumption	100 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Number of products on MCB of 16 A type	е В -
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover shape	-
Optical cover finish	Frosted
Overall length	500 mm
Overall width	84 mm
Overall height	349 mm
Effective projected area	0.12 m²
Dimensions (Height x Width x Depth)	349 x 84 x 500 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 15 kV
	differential mode and 15 kV common mode
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%
<b>Application Conditions</b>	
Maximum dim level	Not applicable
Product Data	
Order product name	BVP381 LED130/CW 100W 220-240V SWB
	GM
Full product name	BVP381 LED130/CW 100W 220-240V SWB
	GM
Full product code	871016334421800
Order code	911401609805
Material Nr. (12NC)	911401609805
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163344218
Numerator - Packs per outer box	1
EAN/UPC - Case	8710163344218

