



# Tango G3 – BVP38x

## BVP381 LED130/WW 100W 220–240V SWB GM

Tango G3 – BVP38x, 13000 lm, 100 W, Warm white, Symmetrical wide beam, 85° x 85°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

### Product data

| General Information      |           |                                    |                                |
|--------------------------|-----------|------------------------------------|--------------------------------|
| Lamp family code         | -         | Standard tilt angle posttop        | -                              |
| Light source replaceable | Yes       | Standard tilt angle side entry     | -                              |
| Number of gear units     | -         | Correlated Color Temperature (Nom) | 3000 K                         |
| Driver included          | Yes       | Luminous Efficacy (rated) (Nom)    | 130 lm/W                       |
| Light source engine type | LED       | Color rendering index (CRI)        | 70                             |
| Lighting Technology      | LED       | Light source color                 | Warm white                     |
| CE mark                  | CE mark   | Optical cover type                 | Polycarbonate micro lens optic |
| Warranty period          | 3 years   | Luminaire light beam spread        | 85° x 85°                      |
| Flammability mark        | -         | Optic type outdoor                 | Symmetrical wide beam          |
| ENEC mark                | -         |                                    |                                |
| EU RoHS compliant        | No        |                                    |                                |
| Light Technical          |           | Operating and Electrical           |                                |
| Luminous Flux            | 13,000 lm | Input Voltage                      | 220–240 V                      |
|                          |           | Line Frequency                     | 50 or 60 Hz                    |
|                          |           | Initial CLO power consumption      | - W                            |
|                          |           | Average CLO power consumption      | - W                            |

## Tango G3 - BVP38x

|  |                          |
|--|--------------------------|
| End CLO power consumption                | - W                      |
| Power Consumption                        | 100 W                    |
| Power Factor (Fraction)                  | 0.95                     |
| Connection                               | Flying leads/wires       |
| Cable                                    | Cable 1.5 m without plug |
| Number of products on MCB of 16 A type B | -                        |

### Temperature

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
|---------------------------|---------------|

### Controls and Dimming

|                               |                            |
|-------------------------------|----------------------------|
| Dimmable                      | No                         |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Control interface             | -                          |
| Constant light output         | No                         |

### Mechanical and Housing

|                                     |                             |
|-------------------------------------|-----------------------------|
| Housing Material                    | Aluminum die cast           |
| Reflector material                  | -                           |
| Optic material                      | Polycarbonate               |
| Optical cover material              | Polycarbonate               |
| Fixation material                   | Steel                       |
| Housing Color                       | Aluminum and gray           |
| Mounting device                     | Mounting bracket adjustable |
| Optical cover shape                 | -                           |
| Optical cover finish                | Frosted                     |
| Overall length                      | 500 mm                      |
| Overall width                       | 84 mm                       |
| Overall height                      | 349 mm                      |
| Effective projected area            | 0.12 m²                     |
| Dimensions (Height x Width x Depth) | 349 x 84 x 500 mm           |

### Approval and Application

|  |  |
|--|--|
| Ingress protection code                | IP66 [Dust penetration-protected, jet-proof]   |
| Mech. impact protection code           | IK08 [5 J vandal-protected]  |
| Surge Protection (Common/Differential) | Luminaire surge protection level until 15 kV differential mode and 15 kV common mode |
| Protection class IEC                   | Safety class I   |

### Initial Performance (IEC Compliant)

|                             |         |
|-----------------------------|---------|
| Luminous flux tolerance     | +/-10%  |
| Initial chromaticity        | SDCM<=7 |
| Power consumption tolerance | +/-10%  |

### Application Conditions

|                   |                |
|-------------------|----------------|
| Maximum dim level | Not applicable |
|-------------------|----------------|

### Product Data

|                                 |                                       |
|---------------------------------|---------------------------------------|
| Order product name              | BVP381 LED130/WW 100W 220-240V SWB GM |
| Full product name               | BVP381 LED130/WW 100W 220-240V SWB GM |
| Full product code               | 872016973080900                       |
| Order code                      | 73080900                              |
| Material Nr. (12NC)             | 911401610605                          |
| Numerator - Quantity Per Pack   | 1                                     |
| EAN/UPC - Product/Case          | 8720169730809                         |
| Numerator - Packs per outer box | 1                                     |
| EAN/UPC - Case                  | 8720169730809                         |

