



Essential SmartBright G2 LED Floodlight

BVP135 LED40/CW 50W 220-240V WB CQC

Essential SmartBright G2 LED Floodlight, 4000 lm, 50 W, 865 cool daylight, Symmetrical wide beam, 100°, Safety class I, Mounting bracket adjustable

Essential SmartBright G2 LED floodlight comes with a compact and sturdy design. It is light weight with die-cast aluminum housing and corrosion-proof powder coating, suitable for general outdoor application. High efficiency designed with latest LED technology, achieves substantial energy savings comparing to conventional floodlights.

Product data

General Information		Optical cover type	
Light source replaceable	No	Luminaire light beam spread	100°
Number of gear units	1 unit	Optic type outdoor	Symmetrical wide beam
Driver included	Yes	Operating and Electrical	
Light source engine type	LED	Input Voltage	220 to 240 V
Lighting Technology	LED	Line Frequency	50 to 60 Hz
CE mark	-	Power Consumption	50 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	4,000 lm	Connection	Flying leads/wires
Correlated Color Temperature (Nom)	6500 K	Cable	Cable 0.25m without plug
Luminous Efficacy (rated) (Nom)	80 lm/W		
Color rendering index (CRI)	>80		
Light source color	865 cool daylight		

Essential SmartBright G2 LED Floodlight

Temperature	
Ambient temperature range	-40 to +45 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Black
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Textured
Overall length	240 mm
Overall width	201 mm
Overall height	38 mm
Effective projected area	0.053 m²
Dimensions (Height x Width x Depth)	38 x 201 x 240 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK06 [1 J]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM <7
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BVP135 LED40/CW 50W 220-240V WB CQC
Full product name	BVP135 LED40/CW 50W 220-240V WB CQC
Full product code	911401613104
Order code	911401613104
Material Nr. (12NC)	911401613104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828625375
Numerator - Packs per outer box	12
EAN/UPC - Case	6923828625498

Dimensional drawing

