



# UNIdot

## BGS300 12xLED-HB-RGB 24V D70

UNIdot, 73 lm, 3.4 W, Red, green and blue, Dynamix DMX, Safety class III

The right façade lighting enhances the ambiance of any space and sparks imagination. Philips UNIdot is just one of the latest innovations in LED ighting that lets you create that perfect atmosphere both for the outdoor and the indoor. Dreamy starry nights, and captivating urban landscapes are all made possible with the smart Philips UNIdot LED lighting system. Flexible and modular, UNIdot lights can be affixed on any challenging façade, fulfilling the most creative lighting design brief. Available in dimmable color options, with light intensity that is easy to adjust, this makes a great replacement for conventional solutions in terms of performance, versatility, light quality and energy savings.

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	No
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	73 lm

Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	-
Luminous Efficacy (rated) (Nom)	21 lm/W
Color rendering index (CRI)	-
Light source color	Red, green and blue
Optical cover type	Polycarbonate bowl/cover frosted
Operating and Electrical	
Input Voltage	24 DC V
Power Consumption	3.4 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires

Cable	Cable 0.3 m without plug
<b>Temperature</b>	
Ambient temperature range	-20 to +50 °C
<b>Controls and Dimming</b>	
Dimmable	Yes
Driver/power unit/transformer	Electronic transformer
Control interface	Dynamix DMX
Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray and white
Mounting device	-
Optical cover shape	Hemispherical flat
Optical cover finish	Frosted
Overall height	52 mm
Overall diameter	70 mm

<b>Approval and Application</b>	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class III

<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

<b>Application Conditions</b>	
Maximum dim level	0% (digital)

<b>Product Data</b>	
Order product name	BGS300 12xLED-HB-RGB 24V D70
Full product name	BGS300 12xLED-HB-RGB 24V D70
Full product code	911401616203
Order code	911401616203
Material Nr. (12NC)	911401616203
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	48

## Dimensional drawing

