



# Tango G3 – BVP38x

## BVP382 LED195/NW 150W 220–240V SMB GM

Tango G3 – BVP38x, 19500 lm, 150 W, Neutral white, Symmetrical medium beam, 50°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

### Product data

| General Information      |           |                                    |                                |
|--------------------------|-----------|------------------------------------|--------------------------------|
| Lamp family code         | -         | Standard tilt angle posttop        | -                              |
| Light source replaceable | Yes       | Standard tilt angle side entry     | -                              |
| Number of gear units     | -         | Correlated Color Temperature (Nom) | 4000 K                         |
| Driver included          | Yes       | Luminous Efficacy (rated) (Nom)    | 130 lm/W                       |
| Light source engine type | LED       | Color rendering index (CRI)        | 70                             |
| Lighting Technology      | LED       | Light source color                 | Neutral white                  |
| CE mark                  | CE mark   | Optical cover type                 | Polycarbonate micro lens optic |
| Warranty period          | 3 years   | Luminaire light beam spread        | 50°                            |
| Flammability mark        | -         | Optic type outdoor                 | Symmetrical medium beam        |
| ENEC mark                | -         | Operating and Electrical           |                                |
| EU RoHS compliant        | No        | Input Voltage                      | 220–240 V                      |
| Light Technical          |           | Line Frequency                     | 50 or 60 Hz                    |
| Luminous Flux            | 19,500 lm | Initial CLO power consumption      | - W                            |
|                          |           | Average CLO power consumption      | - W                            |

Tango G3 - BVP38x

|  |                          |
|--|--------------------------|
| End CLO power consumption                | - W                      |
| Power Consumption                        | 150 W                    |
| Power Factor (Fraction)                  | 0.95                     |
| Connection                               | Flying leads/wires       |
| Cable                                    | Cable 1.5 m without plug |
| Number of products on MCB of 16 A type B | -                        |

Temperature

|                           |               |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
|---------------------------|---------------|

Controls and Dimming

|                               |                            |
|-------------------------------|----------------------------|
| Dimmable                      | No                         |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Control interface             | -                          |
| Constant light output         | No                         |

Mechanical and Housing

|                          |                             |
|--------------------------|-----------------------------|
| Housing Material         | Aluminum die cast           |
| Reflector material       | -                           |
| Optic material           | Polycarbonate               |
| Optical cover material   | Polycarbonate               |
| Fixation material        | Steel                       |
| Housing Color            | Aluminum and gray           |
| Mounting device          | Mounting bracket adjustable |
| Optical cover shape      | -                           |
| Optical cover finish     | Frosted                     |
| Overall length           | 500 mm                      |
| Overall width            | 97 mm                       |
| Overall height           | 498 mm                      |
| Effective projected area | 0.17 m²                     |

|                                     |                   |
|-------------------------------------|-------------------|
| Dimensions (Height x Width x Depth) | 498 x 97 x 500 mm |
|-------------------------------------|-------------------|

Approval and Application

|  |  |
|--|--|
| Ingress protection code                | IP66 [Dust penetration-protected, jet-proof]   |
| Mech. impact protection code           | IK08 [5 J vandal-protected]  |
| Surge Protection (Common/Differential) | Luminaire surge protection level until 15 kV differential mode and 15 kV common mode |
| Protection class IEC                   | Safety class I   |

Initial Performance (IEC Compliant)

|                             |         |
|-----------------------------|---------|
| Luminous flux tolerance     | +/-10%  |
| Initial chromaticity        | SDCM<=7 |
| Power consumption tolerance | +/-10%  |


Application Conditions

|                   |                |
|-------------------|----------------|
| Maximum dim level | Not applicable |
|-------------------|----------------|

Product Data

|                                 |  |
|---------------------------------|--|
| Order product name              | BVP382 LED195/NW 150W 220-240V SMB<br>GM |
| Full product name               | BVP382 LED195/NW 150W 220-240V SMB<br>GM |
| Full product code               | 911401616905                             |
| Order code                      | 911401616905                             |
| Material Nr. (12NC)             | 911401616905                             |
| Numerator - Quantity Per Pack   | 1  |
| Numerator - Packs per outer box | 1  |

Dimensional drawing



## Tango G3 - BVP38x

