



UNistrip G3

BCP280 G3 20LEDHP/3000 L1200 24V W

UNistrip G3, 3560 lm, 40 W, Warm white, Wide beam angle 45°,
Safety class III, Mounting bracket adjustable

UNI strip G3 is a LED wall washer lighting fixture designed for architectural lighting applications. UNistrip G3 offers reliable quality and outstanding performance.

Product data

| General Information | |
|------------------------------------|---|
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Driver included | No |
| Light source engine type | LED |
| Lighting Technology | LED |
| CE mark | CE mark |
| Warranty period | 3 years |
| Flammability mark | For mounting on normally flammable surfaces |
| EU RoHS compliant | Yes |
| | |
| Light Technical | |
| Luminous Flux | 3,560 lm |
| Standard tilt angle posttop | - |
| Standard tilt angle side entry | - |
| Correlated Color Temperature (Nom) | 3000 K |
| Luminous Efficacy (rated) (Nom) | 89 lm/W |
| Color rendering index (CRI) | 80 |
| Light source color | Warm white |
| Optical cover type | Acrylic bowl/cover clear |

| Optic type outdoor | Wide beam angle 45° |
|-------------------------------|--------------------------|
| | |
| Operating and Electrical | |
| Input Voltage | 24 DC V |
| Inrush current | 30 A |
| Inrush time | 0.03 ms |
| Power Consumption | 40 W |
| Power Factor (Fraction) | 0.95 |
| Connection | Flying leads/wires |
| Cable | Cable 1.0 m without plug |
| | |
| Temperature | |
| Ambient temperature range | -40 to +50 °C |
| | |
| Controls and Dimming | |
| Dimmable | No |
| Driver/power unit/transformer | Electronic transformer |
| Control interface | - |
| Constant light output | No |

UNIstrip G3

Mechanical and Housing

| | |
|-------------------------------------|-----------------------------|
| Housing Material | Aluminum extruded |
| Optic material | Acrylate |
| Optical cover material | Acrylate |
| Housing Color | Aluminum and black |
| Mounting device | Mounting bracket adjustable |
| Optical cover shape | Conical |
| Optical cover finish | Clear |
| Overall length | 1,198 mm |
| Overall width | 50 mm |
| Overall height | 65 mm |
| Dimensions (Height x Width x Depth) | 65 x 50 x 1198 mm |

Approval and Application

| | |
|------------------------------|--|
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK06 [1 J] |
| Protection class IEC | Safety class III |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Application Conditions

| | |
|-------------------|----------------|
| Maximum dim level | Not applicable |
|-------------------|----------------|

Product Data

| | |
|---------------------------------|------------------------------------|
| Order product name | BCP280 G3 20LEDHP/3000 L1200 24V W |
| Full product name | BCP280 G3 20LEDHP/3000 L1200 24V W |
| Full product code | 911401623604 |
| Order code | 911401623604 |
| Material Nr. (12NC) | 911401623604 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 8 |

Dimensional drawing

