

UNIstrip G3

BCP280 G3 5LEDHP/4000 L300 24V A DMX

UNI strip G3 is a LED wall washer lighting fixture designed for architectural lighting applications. UNIstrip G3 offers reliable quality and outstanding performance.

Product data

| General Information | |
|-------------------------------|--|
| Light source colour | Neutral white |
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Driver/power unit/transformer | ET [Electronic transformer] |
| Driver included | No |
| Optical cover/lens type | ACC [Acrylic bowl/cover clear] |
| Control interface | Dynamix DMX |
| Connection | Flying leads/wires |
| Cable | Cable 1.0 m without plug (C1K) |
| Protection class IEC | Safety class III (III) |
| Flammability mark | F [For mounting on normally flammable surfaces] |
| CE mark | CE mark |
| Warranty period | 3 years |
| Constant light output | No |
| EU RoHS compliant | Yes |
| LED engine type | LED |

| Light Technical | |
|--------------------------------|---|
| Standard tilt angle post-top | - |
| Standard tilt angle side entry | - |

| Operating and Electrical | |
|--------------------------|---------|
| Input voltage | 24 DC V |
| Inrush current | 30 A |

| | |
|---------------------|---------|
| Inrush time | 0.03 ms |
| Power factor (min.) | 0.95 |

| Controls and Dimming | |
|----------------------|-----|
| Dimmable | Yes |

| Mechanical and Housing | |
|-----------------------------|------------------------------------|
| Housing material | Aluminum extruded |
| Optic material | Acrylate |
| Optical cover/lens material | Acrylate |
| Mounting device | MBA [Mounting bracket adjustable] |
| Optical cover/lens shape | Conical |
| Optical cover/lens finish | Clear |
| Overall length | 335 mm |
| Overall width | 50 mm |
| Overall height | 65 mm |
| Colour | Aluminum and black |

| Approval and Application | |
|------------------------------|---|
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK06 [1 J] |

| Initial Performance (IEC Compliant) | |
|-------------------------------------|---------|
| Initial luminous flux | 1000 lm |
| Luminous flux tolerance | +/-10% |

UNIstrip G3

| | |
|--------------------------------|----------|
| Initial LED luminaire efficacy | 104 lm/W |
| Init. Corr. colour temperature | 4000 K |
| Init. colour rendering index | 80 |
| Initial input power | 9.6 W |
| Power consumption tolerance | +/-10% |

Application Conditions

| | |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
| Maximum dimming level | 0% (digital) |


Product Data

| | |
|-------------------|--------------|
| Full product code | 911401624204 |
|-------------------|--------------|

| | |
|---------------------------------|--------------------------------------|
| Order product name | BCP280 G3 5LEDHP/4000 L300 24V A DMX |
| Order code | 01624204 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 8 |
| Material no. (12NC) | 911401624204 |
| Net weight (piece) | 0.550 kg |



Dimensional drawing



BCP280/383/384/385 UNIstrip G3

