



CoreLine Downlight

DN140B LED10S/840 PSD-E C IP54

CoreLine Downlight, 11.5 W, D150 mm, 1100 lm, 4000 K, DALI, High-gloss reflector, Clear, IP20/54

The CoreLine Downlight range of recessed luminaires is designed to replace CFL-ni/CFL-i based downlight luminaires. Their attractive TCO helps customers to make the switch to LED. These luminaires create a natural lighting effect for use in general lighting applications. They also deliver instant energy savings and have a much longer lifetime, creating a real value-for-money and environmentally friendly solution. They are easy to install thanks to their standard cut-out size and push-in connectors.

Product data

General Information			
Light source replaceable	No	Flammability mark	For mounting on normally flammable surfaces
Number of gear units	Unit	ENEC mark	-
Driver included	Yes	Glow-wire test	Temperature 850 °C, duration 30 s
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.	EU RoHS compliant	Yes
Product family code	DN140B [Coreline Downlight Gen4]	Light Technical	
Lighting Technology	LED	Luminous Flux	1,100 lm
Value ladder	Performance	Saturated Red (R9)	<50
CE mark	Yes	Correlated Colour Temperature	4000 K
Warranty period	5 years	Luminous efficacy (rated) (nom.)	96 lm/W
		Colour rendering index (CRI)	≥80
		Flickering value (PstLM)	1
		Stroboscopic effect	0.4
		Beam angle of light source	120 degree(s)
		Light source colour	840 neutral white

CoreLine Downlight

Optic type	-
Luminaire light beam spread	60°
Unified Glare Rating (CEN)	22

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Inrush current	20.4 A
Inrush time	0.195 ms
Power Consumption	11.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	24

Temperature

Ambient temperature range	-20 to +40 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface external
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing material	Aluminium
Reflector material	Aluminium and polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Glass
Fixation material	Steel
Housing Colour	White
Optical cover/lens finish	Clear
Reflector finish	High-gloss reflector
Overall length	0 mm
Overall width	0 mm
Overall height	100 mm
Overall diameter	162 mm

Dimensions (height x width x depth)	100 x 0 x 0 mm
-------------------------------------	----------------

Approval and Application

Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.379,0.379) SDCM≤5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	1 %
Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L70

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data

Order product name	DN140B LED10S/840 PSD-E C IP54
Full product name	DN140B LED10S/840 PSD-E C IP54
Full EOC	871016332607800
Order code	32607800
Material no. (12 NC)	911401633705
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8710163326078
Numerator – packs per outer box	1
EAN/UPC - Case	8710163326078

CoreLine Downlight

Dimensional drawing

