



SportsStar- BVP621/BVP622/ EVP622

BVP621 LED480/CW 480W 220-240V T5R

SportsStar-BVP621/BVP622/EVP622, 48000 lm, 480 W, Cool white, Symmetrical medium beam, 50° x 50°, Safety class I, Mounting bracket adjustable

Philips SportsStar LED Floodlight sets the standard in high quality optical distribution with high performance and low light pollution (or effective light control). From Sports to Area Lighting, our system, including the high masts needed, projects the light exactly where it should be going. Choose the right illumination levels for any given setting with Philips SportsStar LED Floodlight.

Product data

General Information		Operating and Electrical	
Light source replaceable	Yes	Luminous Efficacy (rated) (Nom)	100 lm/W
Number of gear units	1 unit	Color rendering index (CRI)	70
Driver included	Yes	Light source color	Cool white
Light source engine type	LED	Optical cover type	Polycarbonate micro lens optic
Lighting Technology	LED	Luminaire light beam spread	50° x 50°
CE mark	-	Optic type outdoor	Symmetrical medium beam
Warranty period	3 years		
Light Technical		Input Voltage	220 to 240 V
Luminous Flux	48,000 lm	Line Frequency	50 or 60 Hz
Correlated Color Temperature (Nom)	5700 K	Power Consumption	480 W
		Power Factor (Fraction)	0.95

SportsStar-BVP621/BVP622/EVP622

Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Mounting device	Mounting bracket adjustable
Optical cover finish	Frosted
Overall length	680 mm
Overall width	520 mm
Overall height	307 mm
Effective projected area	0.42 m ²

Dimensions (Height x Width x Depth)	307 x 520 x 680 mm
-------------------------------------	--------------------

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP621 LED480/CW 480W 220-240V T5R
Full product name	BVP621 LED480/CW 480W 220-240V T5R
Full product code	911401634903
Order code	911401634903
Material Nr. (12NC)	911401634903
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

