



Tango G3 – BVP38x

BVP382 LED140/CW 120W 220-240V AMB

Tango G3 – BVP38x, 14400 lm, 120 W, Cool white, Asymmetrical medium beam, 40° x 80°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

Product data

General Information		Operating and Electrical	
Light source replaceable	Yes	Luminaire light beam spread	40° x 80°
Driver included	Yes	Optic type outdoor	Asymmetrical medium beam
Light source engine type	LED	Input Voltage	220-240 V
Lighting Technology	LED	Line Frequency	50 or 60 Hz
CE mark	-	Power Consumption	120 W
Warranty period	3 years	Power Factor (Fraction)	0.95
Light Technical		Connection	Flying leads/wires
Luminous Flux	14,400 lm	Cable	Cable 0.5 m without plug
Correlated Color Temperature (Nom)	5700 K	Temperature	
Luminous Efficacy (rated) (Nom)	120 lm/W	Ambient temperature range	-40 to +50 °C
Color rendering index (CRI)	70		
Light source color	Cool white		
Optical cover type	Polycarbonate micro lens optic		

Tango G3 - BVP38x

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Frosted
Overall length	500 mm
Overall width	97 mm
Overall height	498 mm
Effective projected area	0.17 m ²
Dimensions (Height x Width x Depth)	498 x 97 x 500 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
-------------------------	----------------------------------------------

Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP382 LED140/CW 120W 220-240V AMB
Full product name	BVP382 LED140/CW 120W 220-240V AMB
Full product code	911401654403
Order code	911401654403
Material Nr. (12NC)	911401654403
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

