



Tango G3 - BVP38x

BVP381 LED60/NW 50W 220-240V SWB

Tango G3 - BVP38x, 6000 lm, 50 W, Neutral white, Symmetrical wide beam, 85° x 85°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

Product data

General Information		Optic type outdoor	
Light source replaceable	Yes	Symmetrical wide beam	
Driver included	Yes	Operating and Electrical	
Light source engine type	LED	Input Voltage	220-240 V
Lighting Technology	LED	Line Frequency	50 or 60 Hz
Warranty period	3 years	Power Consumption	50 W
Light Technical		Power Factor (Fraction)	0.95
Luminous Flux	6,000 lm	Connection	Flying leads/wires
Correlated Color Temperature (Nom)	4000 K	Cable	Cable 0.5 m without plug
Luminous Efficacy (rated) (Nom)	120 lm/W	Temperature	
Color rendering index (CRI)	70	Ambient temperature range	-40 to +50 °C
Light source color	Neutral white	Controls and Dimming	
Optical cover type	Polycarbonate micro lens optic	Dimmable	No
Luminaire light beam spread	85° x 85°		

Tango G3 - BVP38x

Driver/power unit/transformer	Power supply unit (On/Off)
-------------------------------	----------------------------

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Frosted
Overall length	500 mm
Overall width	84 mm
Overall height	349 mm
Effective projected area	0.12 m ²
Dimensions (Height x Width x Depth)	349 x 84 x 500 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
--	--

Protection class IEC	Safety class I
----------------------	----------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP381 LED60/NW 50W 220-240V SWB
Full product name	BVP381 LED60/NW 50W 220-240V SWB
Full product code	911401654803
Order code	911401654803
Material Nr. (12NC)	911401654803
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

