



Tango G3 – BVP38x

BVP381 LED111/WW 100W 220-240V SWB

Tango G3 – BVP38x, 11000 lm, 100 W, Warm white, Symmetrical wide beam, 85° x 85°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

Product data

General Information		Optic type outdoor	
Light source replaceable	Yes	Symmetrical wide beam	
Driver included	Yes		
Light source engine type	LED	Operating and Electrical	
Lighting Technology	LED	Input Voltage	220-240 V
Warranty period	3 years	Line Frequency	50 or 60 Hz
		Power Consumption	100 W
		Power Factor (Fraction)	0.95
		Connection	Flying leads/wires
		Cable	Cable 0.5 m without plug
Light Technical		Temperature	
Luminous Flux	11,000 lm	Ambient temperature range	-40 to +50 °C
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	110 lm/W	Controls and Dimming	
Color rendering index (CRI)	70	Dimmable	No
Light source color	Warm white		
Optical cover type	Polycarbonate micro lens optic		
Luminaire light beam spread	85° x 85°		

Tango G3 - BVP38x

Driver/power unit/transformer	Power supply unit (On/Off)
Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Frosted
Overall length	500 mm
Overall width	84 mm
Overall height	349 mm
Effective projected area	0.12 m²
Dimensions (Height x Width x Depth)	349 x 84 x 500 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP381 LED111/WW 100W 220-240V SWB
Full product name	BVP381 LED111/WW 100W 220-240V SWB
Full product code	911401656503
Order code	911401656503
Material Nr. (12NC)	911401656503
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

