



Tango G3 – BVP38x

BVP382 LED240/NW 200W 220-240V AMB

Tango G3 – BVP38x, 24000 lm, 200 W, Neutral white, Asymmetrical medium beam, 40° x 80°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

Product data

General Information		Optic type outdoor	
Light source replaceable	Yes	Asymmetrical medium beam	
Driver included	Yes		
Light source engine type	LED		
Lighting Technology	LED		
Warranty period	3 years		
Light Technical		Operating and Electrical	
Luminous Flux	24,000 lm	Input Voltage	220-240 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 or 60 Hz
Luminous Efficacy (rated) (Nom)	120 lm/W	Power Consumption	200 W
Color rendering index (CRI)	70	Power Factor (Fraction)	0.95
Light source color	Neutral white	Connection	Flying leads/wires
Optical cover type	Polycarbonate micro lens optic	Cable	Cable 0.5 m without plug
Luminaire light beam spread	40° x 80°		
		Temperature	
		Ambient temperature range	-40 to +50 °C
		Controls and Dimming	
		Dimmable	No

Tango G3 - BVP38x

Driver/power unit/transformer	Power supply unit (On/Off)
Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Frosted
Overall length	500 mm
Overall width	97 mm
Overall height	498 mm
Effective projected area	0.17 m²
Dimensions (Height x Width x Depth)	498 x 97 x 500 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%
Product Data	
Order product name	BVP382 LED240/NW 200W 220-240V AMB
Full product name	BVP382 LED240/NW 200W 220-240V AMB
Full product code	911401656803
Order code	911401656803
Material Nr. (12NC)	911401656803
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

