



Tango G3 – BVP38x

BVP382 LED130/WW 120W 220-240V AMB

Tango G3 – BVP38x, 13200 lm, 120 W, Warm white, Asymmetrical medium beam, 40° x 80°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

Product data

General Information			
Light source replaceable	Yes	Luminaire light beam spread	40° x 80°
Driver included	Yes	Optic type outdoor	Asymmetrical medium beam
Light source engine type	LED	Operating and Electrical	
Lighting Technology	LED	Input Voltage	220-240 V
CE mark	-	Line Frequency	50 or 60 Hz
Warranty period	3 years	Power Consumption	120 W
Light Technical		Power Factor (Fraction)	0.95
Luminous Flux	13,200 lm	Connection	Flying leads/wires
Correlated Color Temperature (Nom)	3000 K	Cable	Cable 0.5 m without plug
Luminous Efficacy (rated) (Nom)	110 lm/W	Temperature	
Color rendering index (CRI)	70	Ambient temperature range	-40 to +50 °C
Light source color	Warm white		
Optical cover type	Polycarbonate micro lens optic		

Tango G3 - BVP38x

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-

Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Frosted
Overall length	500 mm
Overall width	97 mm
Overall height	498 mm
Effective projected area	0.17 m ²
Dimensions (Height x Width x Depth)	498 x 97 x 500 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP382 LED130/WW 120W 220-240V AMB
Full product name	BVP382 LED130/WW 120W 220-240V AMB
Full product code	911401657503
Order code	911401657503
Material Nr. (12NC)	911401657503
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

