



# Tango G3 – BVP38x

## BVP382 LED223/WW 200W 220-240V AMB

Tango G3 – BVP38x, 22000 lm, 200 W, Warm white, Asymmetrical medium beam, 40° x 80°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

### Product data

<b>General Information</b>		<b>Optic type outdoor</b>	
Light source replaceable	Yes	Asymmetrical medium beam	
Driver included	Yes		
Light source engine type	LED	<b>Operating and Electrical</b>	
Lighting Technology	LED	Input Voltage	220-240 V
Warranty period	3 years	Line Frequency	50 or 60 Hz
		Power Consumption	200 W
		Power Factor (Fraction)	0.95
		Connection	Flying leads/wires
		Cable	Cable 0.5 m without plug
<b>Light Technical</b>		<b>Temperature</b>	
Luminous Flux	22,000 lm	Ambient temperature range	-40 to +50 °C
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	110 lm/W	<b>Controls and Dimming</b>	
Color rendering index (CRI)	70	Dimmable	No
Light source color	Warm white		
Optical cover type	Polycarbonate micro lens optic		
Luminaire light beam spread	40° x 80°		

## Tango G3 - BVP38x

Driver/power unit/transformer	Power supply unit (On/Off)
<b>Mechanical and Housing</b>	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Frosted
Overall length	500 mm
Overall width	97 mm
Overall height	498 mm
Effective projected area	0.17 m²
Dimensions (Height x Width x Depth)	498 x 97 x 500 mm
<b>Approval and Application</b>	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

<b>Surge Protection (Common/Differential)</b>	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
<b>Protection class IEC</b>	Safety class I
<b>Initial Performance (IEC Compliant)</b>	
<b>Luminous flux tolerance</b>	+/-10%
<b>Initial chromaticity</b>	SDCM<=7
<b>Power consumption tolerance</b>	+/-10%
<b>Product Data</b>	
<b>Order product name</b>	BVP382 LED223/WW 200W 220-240V AMB
<b>Full product name</b>	BVP382 LED223/WW 200W 220-240V AMB
<b>Full product code</b>	911401658003
<b>Order code</b>	911401658003
<b>Material Nr. (12NC)</b>	911401658003
<b>Numerator - Quantity Per Pack</b>	1
<b>Numerator - Packs per outer box</b>	1

### Dimensional drawing

