



# Tango G2 LED

## BVP283 LED245/NW 245W 220-240V SWB

Tango G2 LED, 24500 lm, 245 W, 740 neutral white, Symmetrical wide beam, 30° x 80°, Safety class I, Mounting bracket adjustable

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

### Product data

General Information	
Light source replaceable	Yes
Driver included	Yes
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Warranty period	3 years
Light Technical	
Luminous Flux	24,500 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	>70
Light source color	740 neutral white
Optical cover type	Glass

Luminaire light beam spread	30° x 80°
Optic type outdoor	Symmetrical wide beam
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	245 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Temperature	
Ambient temperature range	-40 to +45 °C

# Tango G2 LED

<b>Controls and Dimming</b>	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

<b>Mechanical and Housing</b>	
Housing Material	Aluminum die cast
Optic material	Polymethyl methacrylate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Overall length	480 mm
Overall width	655 mm
Overall height	60 mm
Effective projected area	0.25 m²
Dimensions (Height x Width x Depth)	60 x 655 x 480 mm

<b>Approval and Application</b>	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]

Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I

<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%

<b>Application Conditions</b>	
Maximum dim level	Not applicable

<b>Product Data</b>	
Order product name	BVP283 LED245/NW 245W 220-240V SWB
Full product name	BVP283 LED245/NW 245W 220-240V SWB
Full product code	911401669802
Order code	01669802
Material Nr. (12NC)	911401669802
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

