



Tango G2 LED

BVP283 LED311/WW 335W 220-240V AWB

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.

Product data

General Information	
Light source color	740 neutral white
Driver included	Yes
Optical cover/lens type	Glass
Control interface	-
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug
Protection class IEC	Safety class I
CE mark	CE mark
Spare parts available	Yes
Operating and Electrical	
Input Voltage	220-240 V
Input Frequency	50 to 60 Hz
Power Factor (Min)	0.95
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Overall length	480 mm
Overall width	655 mm
Overall height	60 mm
Color	Aluminum and gray

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]


Initial Performance (IEC Compliant)	
Initial luminous flux (system flux)	31100 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	90 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	>70
Initial input power	335 W

Tango G2 LED

Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	50000 h
Application Conditions	
Ambient temperature range	-40 to +50 °C
Product Data	
Full product code	911401670002

Order product name	BVP283 LED311/WW 335W 220-240V AWB
Order code	911401670002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911401670002
Net Weight (Piece)	13.200 kg

Dimensional drawing



Tango LED gen2 BVP281-BVP284

