



Tango G2 LED

BVP283 LED293/WW 315W 220-240V AWB

Tango G2 LED is a general purpose LED flood lighting luminaire for various lighting applications, such as area lighting, bill-board, façade, industry area, recreational sports and other general applications. The Tango G2 LED flood light incorporates LED light source, optical system, heat sink and driver into one compact housing. Its specially designed heat sink incorporates aesthetics and functionality to ensure reliability and long lifetime. Tango G2 LED takes advantage of LED technology which provides energy savings and a longer lifetime, bringing area lighting into a new era.


Product data

| General Information | |
|------------------------------|---|
| Driver included | Yes |
| Protection class IEC | Safety class I (I) |
| CE mark | CE mark |
| Spare parts available | Yes |
| Operating and Electrical | |
| Input voltage | 220-240 V |
| Input frequency | 50 to 60 Hz |
| Mechanical and Housing | |
| Housing material | Aluminum extruded |
| Optic material | Polycarbonate |
| Optical cover/lens material | Polycarbonate |
| Approval and Application | |
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK07 [2 J reinforced] |

| Over Time Performance (IEC Compliant) | |
|---------------------------------------|------------------------------------|
| Median useful life L70B50 | 50000 h |
| Application Conditions | |
| Ambient temperature range | -40 to +50 °C |
| Product Data | |
| Full product code | 911401670102 |
| Order product name | BVP283 LED293/WW 315W 220-240V AWB |
| Order code | 911401670102 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 1 |
| Material no. (12NC) | 911401670102 |
| Net weight (piece) | 13.200 kg |

Tango G2 LED

Dimensional drawing



Tango LED gen2 BVP281-BVP284

