



SportsStar- BVP621/BVP622/ EVP622

BVP622 LED739/957 960W S5 DMX RAL9007

SportsStar-BVP621/BVP622/EVP622, 73920 lm, 960 W, Cool white, Beam category S5, 17°, Safety class I, Mounting bracket adjustable

Philips SportsStar LED Floodlight sets the standard in high quality optical distribution with high performance and low light pollution (or effective light control). From Sports to Area Lighting, our system, including the high masts needed, projects the light exactly where it should be going. Choose the right illumination levels for any given setting with Philips SportsStar LED Floodlight.

Product data

General Information			
Light source replaceable	Yes	Luminous Efficacy (rated) (Nom)	77 lm/W
Number of gear units	2 units	Color rendering index (CRI)	90
Driver included	No	Light source color	Cool white
Light source engine type	LED	Optical cover type	Polycarbonate micro lens optic
Lighting Technology	LED	Luminaire light beam spread	17°
CE mark	-	Optic type outdoor	Beam category S5
Warranty period	3 years	Operating and Electrical	
Light Technical		Input Voltage	- V
Luminous Flux	73,920 lm	Line Frequency	- Hz
Correlated Color Temperature (Nom)	5700 K	Power Consumption	960 W
		Power Factor (Fraction)	0.95

SportsStar-BVP621/BVP622/EVP622

Connection	Connection unit 3-pole
Cable	Cable 1.5 m without plug

Temperature

Ambient temperature range	-40 to +55 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover finish	Frosted
Overall length	680 mm
Overall width	740 mm
Overall height	307 mm
Effective projected area	0.42 m²

Dimensions (Height x Width x Depth)	307 x 740 x 680 mm
-------------------------------------	--------------------

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=7
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP622 LED739/957 960W S5 DMX RAL9007
Full product name	BVP622 LED739/957 960W S5 DMX RAL9007
Full product code	911401670703
Order code	911401670703
Material Nr. (12NC)	911401670703
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

