



FlowBase

BWP352 LED66/WW 60W 220-240V DM MP1 R

FlowBase, 6600 lm, 60 W, 730 warm white, Medium beam, Safety class I, Wall-mounting bracket

A lighting design that ensures safety and good visibility is a key element in the success of any tunnel project. Philips FlowBase combines compact design, reliability, and affordability in one complete package to bring the perfect lighting solution for any tunnel application.

Product data

| General Information | |
|------------------------------------|----------------|
| Light source replaceable | No |
| Driver included | Yes |
| Light source engine type | LED |
| CE mark | CE mark |
| Light Technical | |
| Luminous Flux | 6,600 lm |
| Correlated Color Temperature (Nom) | 3000 K |
| Luminous Efficacy (rated) (Nom) | 110 lm/W |
| Color rendering index (CRI) | >70 |
| Light source color | 730 warm white |
| Optic type outdoor | Medium beam |
| Operating and Electrical | |
| Input Voltage | 220-240 V |
| Line Frequency | 50 or 60 Hz |
| Power Consumption | 60 W |
| Power Factor (Fraction) | 0.95 |

| Cable | Cable 0.45 m without plug |
|---------------------------|---------------------------|
| Temperature | |
| Ambient temperature range | -40 to +50 °C |
| Controls and Dimming | |
| Dimmable | No |
| Constant light output | No |
| Mechanical and Housing | |
| Housing Material | Aluminum die cast |
| Optic material | Polycarbonate |
| Optical cover material | Polycarbonate |
| Housing Color | Grey |
| Mounting device | Wall-mounting bracket |
| Optical cover shape | Ball, globular |
| Overall length | 429 mm |
| Overall width | 150 mm |
| Overall height | 122 mm |

Dimensions (Height x Width x Depth) 122 x 150 x 429 mm

Approval and Application

Ingress protection code IP66 [Dust penetration-protected, jet-proof]

Mech. impact protection code IK08 [5 J vandal-protected]

Protection class IEC Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-5%

Initial chromaticity (0.433, 0.401) SDCM>5

Power consumption tolerance +/-5%

Product Data

Order product name BWP352 LED66/WW 60W 220-240V DM MP1 R

Full product name BWP352 LED66/WW 60W 220-240V DM MP1 R

Full product code 911401672803

Order code 911401672803

Material Nr. (12NC) 911401672803

Numerator - Quantity Per Pack 1

Numerator - Packs per outer box 1

Dimensional drawing

