



SmartBright LED Floodlight

BVP172 LED43/WW 50W WB GREY SAA KC

SmartBright LED Floodlight, 4300 lm, 50 W, 730 warm white, 30° x 80°, Safety class I, Mounting bracket adjustable

The SmartBright LED Floodlight is a versatile floodlight engineered to deliver significant energy savings, an ideal solution for diverse floodlighting applications. The product is also designed to meet relevant performance and safety standards, offering you reliable and long-lasting performance.

Product data

General Information		Luminaire light beam spread	
Lamp family code	LED43 [LED module 4300 lm]	30° x 80°	
Light source replaceable	No	Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 or 60 Hz
Lighting Technology	LED	Inrush current	2.9 A
Flammability mark	For mounting on normally flammable surfaces	Inrush time	0.000225 ms
CE mark	CE mark	Power Consumption	50 W
Light Technical		Power Factor (Fraction)	0.9
Luminous Flux	4,300 lm	Connection	Flying leads/wires
Correlated Color Temperature (Nom)	3000 K	Cable	Cable 0.6 m without plug
Luminous Efficacy (rated) (Nom)	86 lm/W	Number of products on MCB of 16 A type B 40	
Color rendering index (CRI)	>70	Temperature	
Light source color	730 warm white	Ambient temperature range	-40 to +45 °C
Optical cover type	Polycarbonate bowl/cover UV-resistant		

SmartBright LED Floodlight

Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Frosted
Overall length	270 mm
Overall width	202 mm
Overall height	38 mm
Effective projected area	0.0729 m²
Dimensions (Height x Width x Depth)	38 x 202 x 270 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Surge Protection (Common/Differential)	4/2 kV

Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BVP172 LED43/WW 50W WB GREY SAA KC
Full product name	BVP172 LED43/WW 50W WB GREY SAA KC
Full product code	871016332084799
Order code	911401674004
Material Nr. (12NC)	911401674004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163320847
Numerator - Packs per outer box	8
EAN/UPC - Case	8710163321448

Dimensional drawing

