



# RoadFlair

## BRP393 LED228/NW 190W 220-240V DM MP1 GC

RoadFlair, 22800 lm, 190 W, 740 neutral white, Medium beam,  
Safety class I, Side-entry for diameter 48 to 60 mm

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

### Product data

<b>General Information</b>		<b>Optic type outdoor</b>	
Light source replaceable	No	Medium beam	
Driver included	Yes	<b>Operating and Electrical</b>	
Light source engine type	LED	Input Voltage	220-240 V
CE mark	CE mark	Line Frequency	50 or 60 Hz
<b>Light Technical</b>		Power Consumption	190 W
Luminous Flux	22,800 lm	Power Factor (Fraction)	0.95
Standard tilt angle side entry	5°	Connection	Mains outlet socket
Correlated Color Temperature (Nom)	4000 K	Cable	Cable 0.5 m without plug
Luminous Efficacy (rated) (Nom)	120 lm/W	<b>Temperature</b>	
Color rendering index (CRI)	>70	Ambient temperature range	-30 to +50 °C
Light source color	740 neutral white	<b>Controls and Dimming</b>	
Optical cover type	Polycarbonate micro lens optic	Dimmable	No

Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Side-entry for diameter 48 to 60 mm
Optical cover shape	Ball, globular
Overall length	650 mm
Overall width	295 mm
Overall height	86 mm
Dimensions (Height x Width x Depth)	86 x 295 x 650 mm

## Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Protection class IEC	Safety class I
----------------------	----------------

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	(0.433, 0.401) SDCM>5
Power consumption tolerance	+/-5%

## Product Data

Order product name	BRP393 LED228/NW 190W 220-240V DM MP1 GC
Full product name	BRP393 LED228/NW 190W 220-240V DM MP1 GC
Full product code	911401674803
Order code	911401674803
Material Nr. (12NC)	911401674803
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

