



Tango G3 - BVP38x

BVP383 LED360/NW 320W 220-240V AMB

Tango LED G3 é a solução ideal para diversas aplicações de iluminação externa com excelente eficiência energética. Incorpora a fonte de luz LED, sistema ótico, dissipador térmico e driver em um compartimento robusto e compacto que atende a todos os padrões de segurança mundialmente reconhecidos. Seu dissipador térmico especialmente desenvolvido incorpora estética e funcionalidade para garantir excelente confiabilidade. Desenvolvida com tecnologia LED, esta luminária oferece desempenho superior e vida útil prolongada, o que leva a iluminação externa a outro nível.

Dados do produto

General Information	
Light source color	NW
Light source replaceable	Sim
Driver/power unit/transformer	PSU [Fonte de alimentação]
Driver included	Sim
Tipo de acessório de lente/difusor ótico	PC-MLO [Óptica com microlente de policarbonato]
Luminaire light beam spread	35° x 100°
Connection	Flying leads/wires
Cable	Cabo de 0,5 m sem plugue
Protection class IEC	CLI (I)
Warranty period	3 years
Optic type outdoor	Facho médio assimétrico
LED engine type	LED
Operating and Electrical	
Input Voltage	220-240 V
Input Frequency	50 ou 60 Hz

Power Factor (Min)	0.95
Controls and Dimming	
Dimmable	Não
Mechanical and Housing	
Housing Material	Aluminum die-cast
Optic material	PC
Optical cover/lens material	PC
Fixation material	Steel
Mounting device	MBA [Suporte de montagem regulável]
Acabamento da lente/difusor ótico	Frosted
Comprimento total	591 mm
Largura total	114 mm
Altura total	603 mm
Effective projected area	0,29 m ²
Cor	ALU-GR

Tango G3 - BVP38x

Approval and Application

Ingress protection code	IP66 [IP66]
Mech. impact protection code	IK08 [IK08]
Surge Protection (Common/Differential)	Surge protection level until 10 kV

Initial Performance (IEC Compliant)

Initial luminous flux	36000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	110 lm/W
Init. Corr. Temperatura de cor	4000 K
Init. Índice de reprodução de cor	70
Initial chromaticity	SDCM<=7
Initial input power	320 W
Power consumption tolerance	+/-10%

Application Conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Product Data

Full product code	911401682403
Order product name	BVP383 LED360/NW 320W 220-240V AMB
Order code	911401682403
Local Code	911401682403
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911401682403
Net Weight (Piece)	12,499 kg



Desenho dimensional



Tango G3 - BVP38x

