



Tango G3 – BVP38x

BVP383 LED450/NW 400W 220-240V NB GM

Tango G3 – BVP38x, 45000 lm, 400 W, Neutral white, Narrow beam, 13°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

Product data

General Information	
Lamp family code	-
Light source replaceable	Yes
Driver included	Yes
Light source engine type	LED
Lighting Technology	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	-
ENEC mark	-
EU RoHS compliant	No
Light Technical	
Luminous Flux	45,000 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-

Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color rendering index (CRI)	>70
Light source color	Neutral white
Optical cover type	Polycarbonate micro lens optic
Luminaire light beam spread	13°
Optic type outdoor	Narrow beam
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	400 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug

Tango G3 - BVP38x

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover shape	-
Optical cover finish	Frosted
Overall length	591 mm
Overall width	114 mm
Overall height	603 mm
Effective projected area	0.29 m²
Dimensions (Height x Width x Depth)	603 x 114 x 591 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM< 7
Power consumption tolerance	+/-10%

Product Data

Order product name	BVP383 LED450/NW 400W 220-240V NB GM
Full product name	BVP383 LED450/NW 400W 220-240V NB GM
Full product code	911401697703
Order code	01697703
Material Nr. (12NC)	911401697703
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

