



# Tango G3 – BVP38x

## BVP383 LED405/WW 400W 220-240V SWB GM

Tango G3 – BVP38x, 40500 lm, 400 W, Warm white, Symmetrical wide beam, 30° x 80°, Safety class I, Mounting bracket adjustable

The energy-saving Philips Tango G3 LED Floodlight is the ideal solution for a wide range of Area lighting applications. It incorporates the LED light source, optical system, heat sink and driver into one compact and robust housing that meets globally recognized safety standards. Its specially designed heat sink incorporates aesthetics and functionality to ensure excellent reliability. Powered by LED technology, this luminaire delivers superior performance and a longer lifetime, bringing area lighting to a whole new level.

### Product data

General Information			
Lamp family code	-	Standard tilt angle side entry	-
Light source replaceable	Yes	Correlated Color Temperature (Nom)	3000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	100 lm/W
Light source engine type	LED	Color rendering index (CRI)	>70
Lighting Technology	LED	Light source color	Warm white
CE mark	CE mark	Optical cover type	Polycarbonate micro lens optic
Warranty period	3 years	Luminaire light beam spread	30° x 80°
Flammability mark	-	Optic type outdoor	Symmetrical wide beam
ENEC mark	-		
EU RoHS compliant	No	Operating and Electrical	
		Input Voltage	220-240 V
		Line Frequency	50 or 60 Hz
		Power Consumption	400 W
		Power Factor (Fraction)	0.95
		Connection	Flying leads/wires
Light Technical			
Luminous Flux	40,500 lm		
Standard tilt angle posttop	-		

## Tango G3 - BVP38x

Cable	Cable 1.5 m without plug
<b>Temperature</b>	
Ambient temperature range	-40 to +50 °C
<b>Controls and Dimming</b>	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
<b>Mechanical and Housing</b>	
Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Aluminum and gray
Mounting device	Mounting bracket adjustable
Optical cover shape	-
Optical cover finish	Frosted
Overall length	591 mm
Overall width	114 mm
Overall height	603 mm
Effective projected area	0.29 m²
Dimensions (Height x Width x Depth)	603 x 114 x 591 mm

<b>Approval and Application</b>	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 15 kV differential mode and 15 kV common mode
Protection class IEC	Safety class I
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM< 7
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	BVP383 LED405/WW 400W 220-240V SWB GM
Full product name	BVP383 LED405/WW 400W 220-240V SWB GM
Full product code	872016973089200
Order code	73089200
Material Nr. (12NC)	911401699203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169730892
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169730892

