



# LuxSpace CN

## DN478 1xDLED-3000 PSU-E M WH

Power supply unit (On/Off), High-gloss mirror, Black and white

LuxSpace Gen3 is the new LED downlight with extremely high efficacy(up to 100lm/W) delivering substantial energy saving. It adopts a brand-new LED platform and optical technology for visual comfort. It has the wide portfolio with multiple lumen and dimension options and is designed with DALI and IP54 (only front side) versions for various applications

### Warnings and Safety

- 1.The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- 2.For indoor use at room temperature
- 3.When cleaning the product, please use dry soft cotton cloth only
- 4.Don't switch on before complete installation
- 5.If the power cord gets damaged within the warranty period, please have it replaced by Philips nominated dealer
- 6.The luminaire shall, under no circumstances be covered or abutted with building insulation or be installed in a residential installation
- 7.Do not hot swap! LED heat sink module must not be disconnected with line power on failure. To do so may damage the product
- 8.Luminaire must not be used or stored in corrosive environment where hazardous material such as Sulphur, Chlorine, Phthalates, etc, are present

### Product data

General Information		Light Technical	
Light source replaceable	No	Luminous Flux	600 lumen
Number of gear units	1 unit	Correlated Color Temperature (Nom)	3000 K
Driver included	Yes	Luminous Efficacy (rated) (Nom)	85.7 lm/W
Warranty period	3 years	Color rendering index (CRI)	>80
Glow-wire test	Temperature 750 °C, duration 5 s	Light source color	830 warm white
		Optic type	High-gloss mirror

Luminaire light beam spread	60°
<b>Operating and Electrical</b>	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	20 A
Inrush time	0.15 ms
Power Consumption	7 W
Power Factor (Fraction)	0.9
Cable	Cable with plug
Number of products on MCB of 16 A type B 50	
<b>Temperature</b>	
Ambient temperature range	-20 to +40 °C
<b>Controls and Dimming</b>	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Aluminum die cast
Reflector material	Aluminum
Optic material	Polycarbonate
Housing Color	Black and white
Overall height	75 mm
Overall diameter	137 mm
<b>Approval and Application</b>	
Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-7.5%
Initial chromaticity	(0.44, 0.40) SDCM <3
Power consumption tolerance	+/-10%
<b>Over Time Performance (IEC Compliant)</b>	
Driver failure rate at 5000 h	1.00 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	40,000 hour(s)
Median useful life L90B50	20,000 hour(s)
<b>Application Conditions</b>	
Suitable for random switching	No
<b>Product Data</b>	
Full product code	911401701512
Order product name	DN478 1xDLED-3000 PSU-E M WH
Order code	911401701512
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8
Material Nr. (12NC)	911401701512
Full product name	DN478 1xDLED-3000 PSU-E M WH

Dimensional drawing



