



Essential SmartBright G3 LED Downlight DN029B

DN029B-2 LED12/CCT PSR-E D150 CAU

Power supply unit

Essential SmartBright Downlight G3 family is the perfect energy efficient LED replacement for conventional downlights. It offers three solutions:;Solution 1;The energy efficient LED replacement for conventional downlights;Essential SmartBright Downlight G3 DN029B-1–trailing and leading edge dimmable downlight is the ideal functional replacement for conventional downlights. This affordable and easy to install fitting delivers high energy savings without compromising on light quality.;Solution 2;Select the right colour temperature to suit your style;This hassle-free Essential SmartBright DN029B-2 downlight provides you with the flexibility to select the perfect colour temperature (Warm White/Cool White/Day Light) for the application. Integrated with trailing/leading edge dimming capability, this affordable and easy to install fitting delivers high energy savings without compromising on light quality.;Solution 3;Enjoy the flexibility of a dimmable fitting without paying more;Essential SmartBright DN029B-3 step dimming downlight is the perfect hassle-free replacement for conventional dimmable downlights. Adjust the light level straight from the switch and save cost with installation as a dimmer unit is not required.

Product data

General Information			
Light source replaceable	No	Driver included	Yes
Number of gear units	1 unit	Control interface	DALI
Driver/power unit/transformer	Power supply unit	Cable	Cable 1.2 m with plug
		Protection class IEC	Safety class II

Essential SmartBright G3 LED Downlight DN029B

Warranty period	3 years
Constant light output	No

Operating and Electrical

Input Voltage	220-240 V
Input Frequency	50 or 60 Hz
Inrush current	2.8 A
Inrush time	0.04 ms
Power Factor (Min)	0.8

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Housing Material	Polybutylene-terephthalate
Optical cover/lens material	Polycarbonate
Overall height	64 mm
Overall diameter	175 mm

Approval and Application

Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
-------------------------	---

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1200 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	86 lm/W

Init. Corr. Color Temperature	3000, 4300 and 6500 K
Init. Color Rendering Index	80
Initial chromaticity	SDCM<5
Initial input power	14 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	25000 h
---------------------------	---------

Application Conditions


Ambient temperature range	-20 to +40 °C
Maximum dim level	10% (depends on dimmer, ELV)

Product Data

Full product code	911401713872
Order product name	DN029B-2 LED12/CCT PSR-E D150 CAU
EAN/UPC - Product	8710163317182
Order code	911401713872
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	911401713872
Net Weight (Piece)	0.380 kg



Dimensional drawing



DN029B-1/2/3 LED8 D90 CAU

Essential SmartBright G3 LED Downlight DN029B

