



UniLinear Flex IP65



BGC201 400LM 4000K L5000

UniLinear Flex IP65, 2000 lm, 18 W, 840 neutral white, 110° x 110°, depends on driver (1-10V, DALI...), Safety class III, Allen screw fixation

UNILinear Flex IP65 is new type waterproof and anti-dust LED strips with state-of-the-art process technology to guarantee lighting performance. Thanks to wrap with anti-UV silicon tube and slot inside for LED PCB fixation, it not only ensure high quality of waterproof performance but also lighting color consistency for attractive light effect. It's an ideal solution for decoration lighting and guidance lighting outdoors, various lumen package and multiple CCT for the option.

Warnings and Safety

- Not allow to be cut otherwise waterproof failiure

Product data

General Information		Color rendering index (CRI)	
Light source replaceable	No		≥80
Driver included	No	Light source color	840 neutral white
Light source engine type	LED	Optical cover type	Without lens
Lighting Technology	LED	Luminaire light beam spread	110° x 110°
CE mark	CE mark	Operating and Electrical	
Flammability mark	For mounting on normally flammable surfaces	Input Voltage	24 V
Light Technical		Line Frequency	0 Hz
Luminous Flux	2,000 lm	Average CLO power consumption	18 W
Standard tilt angle posttop	-	Power Consumption	18 W
Correlated Color Temperature (Nom)	4000 K	Power Factor (Fraction)	1
Luminous Efficacy (rated) (Nom)	80 lm/W	Connection	Flying leads/wires

UniLinear Flex IP65

Cable	Cable 0.3 m without plug
Temperature	
Ambient temperature range	-40 to +45 °C
Controls and Dimming	
Dimmable	Yes
Control interface	depends on driver (1-10V, DALI...)
Constant light output	No
Mechanical and Housing	
Housing Material	Silicon
Optical cover material	Silicon tube
Housing Color	Clear
Mounting device	Allen screw fixation
Optical cover finish	Clear
Overall length	5,050 mm
Overall width	10 mm
Overall height	4.4 mm
Dimensions (Height x Width x Depth)	4 x 10 x 5050 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Energy Efficiency Class	G

Mech. impact protection code	IK03 [0.3 J]
EPREL Registration Number	733246
Protection class IEC	Safety class III
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-15%
Initial chromaticity	SDCM ≤ 5
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	0% (digital)
Product Data	
Order product name	BGC201 400LM 4000K L5000
Full product name	BGC201 400LM 4000K L5000
Full product code	692382862987899
Order code	911401720182
Material Nr. (12NC)	911401720182
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828629878
Numerator - Packs per outer box	10
EAN/UPC - Case	6923828630003

Dimensional drawing

