



# Greenspace Flex

## RS378B P6 930 PSU-E WB M55

Greenspace Flex, 6 W, 930 warm white, 32°, Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

<b>General Information</b>		<b>Luminaire light beam spread</b>	
Number of gear units	1 unit	32°	
Driver included	Yes		
Light source engine type	LED	<b>Operating and Electrical</b>	
CE mark	-	<b>Input Voltage</b>	
Warranty period	3 years	220 to 240 V	
Flammability mark	-	<b>Line Frequency</b>	
ENEC mark	-	50 or 60 Hz	
Glow-wire test	Temperature 600 °C, duration 30 s	<b>Average CLO power consumption</b>	
EU RoHS compliant	Yes	390 W	
		<b>Power Consumption</b>	
		6 W	
		<b>Power Factor (Fraction)</b>	
		0.9	
		<b>Connection</b>	
		External connector	
		<b>Cable</b>	
		-	
		<b>Number of products on MCB of 16 A type B</b>	
		-	
<b>Light Technical</b>		<b>Temperature</b>	
Luminous Flux	468 lm	<b>Ambient temperature range</b>	
Correlated Color Temperature (Nom)	3000 K	-20 to +45 °C	
Luminous Efficacy (rated) (Nom)	78 lm/W		
Color rendering index (CRI)	>90	<b>Controls and Dimming</b>	
Beam angle of light source	- degree(s)	<b>Dimmable</b>	
Light source color	930 warm white	No	
Optic type	-	<b>Driver/power unit/transformer</b>	
Optical cover type	-	Electronic transformer	
		<b>Control interface</b>	
		-	
		<b>Constant light output</b>	
		No	

Greenspace Flex

Mechanical and Housing	
Housing Material	Aluminum Alloy
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	-
Fixation material	Aluminum
Housing Color	Dark gray
Optical cover finish	-
Overall height	49 mm
Overall diameter	55 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Protection class IEC	Safety class II



Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L80B50	50.000 hour(s)

Application Conditions	
Maximum dim level	Not applicable
Suitable for random switching	No

Product Data	
Order product name	RS378B P6 930 PSU-E WB M55
Full product name	RS378B P6 930 PSU-E WB M55
Full product code	692382864992099
Order code	911401720962
Material Nr. (12NC)	911401720962
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828649920
Numerator - Packs per outer box	48
EAN/UPC - Case	6923828652333

Dimensional drawing



Modular Type	D, mm	H, mm
RS378B P6/P11 M55	55	49
RS378B P15 M55	55	49
RS378B P24 M70	70	90
RS378B P33 M87	87	107
RS378B P42 M102	102	116

