



SmartBright Slim Panel G2

RC091V LED26S/840 PSU W60L60 GM G2

SmartBright Slim Panel G2, 90 lm/W, 840 neutral white

The SmartBright Slim Panel provides the most affordable LED solution. The complete product family delivers multiple mounting types, product dimensions and lumen options. The new generation ensures both higher system efficacy and excellent lighting uniformity.

Product data

General Information		Number of products on MCB of 16 A type B 74	
Light source engine type	LED		
CE mark	CE mark		
Light Technical		Temperature	
Luminous Flux	2,600 lm	Ambient temperature range	-10 to +35 °C
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	90 lm/W	Controls and Dimming	
Color rendering index (CRI)	>80	Dimmable	No
Light source color	840 neutral white	Control interface	-
Optical cover type	Polystyrene bowl/cover prismatic		
Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing Material	Aluminum extruded
Line Frequency	50 or 60 Hz	Optical cover material	Polystyrene
Power Consumption	29 W	Housing Color	White
Power Factor (Fraction)	0.9	Optical cover finish	Frosted
		Approval and Application	
		Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK02 [0.2 J standard]

SmartBright Slim Panel G2

Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	RC091V LED26S/840 PSU W60L60 GM G2
Full product name	RC091V LED26S/840 PSU W60L60 GM G2

Full product code	871016332467800
Order code	911401723772
Material Nr. (12NC)	911401723772
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163324678
Numerator - Packs per outer box	4
EAN/UPC - Case	8710163324678

Dimensional drawing

