



SmartBright Slim Panel G2

RC091V LED26S/840 PSU W60L60 GM G2

SmartBright Slim Panel G2, 90 lm/W, 840 neutral white

SmartBright Slim Panel provides the most affordable LED solution. Complete product family delivers multiple mounting types, product dimensions & lumen options. New generation ensures both higher system efficacy and excellent lighting uniformity.

Product data

General Information		Number of products on MCB of 16 A type B 74	
Light source engine type	LED		
CE mark	CE mark		
Light Technical		Temperature	
Luminous Flux	2,600 lm	Ambient temperature range	-10 to +35 °C
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	90 lm/W	Controls and Dimming	
Color rendering index (CRI)	>80	Dimmable	No
Light source color	840 neutral white	Control interface	-
Optical cover type	Polystyrene bowl/cover prismatic		
Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing Material	Aluminum extruded
Line Frequency	50 or 60 Hz	Optical cover material	Polystyrene
Power Consumption	29 W	Housing Color	White
Power Factor (Fraction)	0.9	Optical cover finish	Frosted
		Approval and Application	
		Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK02 [0.2 J standard]

SmartBright Slim Panel G2

Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	RC091V LED26S/840 PSU W60L60 GM G2
Full product name	RC091V LED26S/840 PSU W60L60 GM G2

Full product code	871016332467800
Order code	911401723772
Material Nr. (12NC)	911401723772
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163324678
Numerator - Packs per outer box	4
EAN/UPC - Case	8710163324678

Dimensional drawing

