



# LED Wall Mount

## BWS151 LED200/WW PSU 220-240V 9006

LED Wall Mount, 240 lm, 5.8 W, 830 warm white, Safety class II, Allen screw fixation

People want to create a pleasant atmosphere around their property – something that will catch visitors' attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience at minimum cost, though without compromising on the quality of the lighting. Combining a simple round design with reliable lighting performance, this low-cost white-light LED wall fixture with opal diffuser delivers a soft light effect with attractive uniformity.

### Product data

<b>General Information</b>		<b>Light source color</b>	
Lamp family code	LED-LP [LED Low Power]	830 warm white	
Light source replaceable	No	<b>Optical cover type</b>	
Number of gear units	1 unit	Polycarbonate bowl/cover UV-resistant	
Driver included	Yes	<b>Operating and Electrical</b>	
Light source engine type	LED	<b>Input Voltage</b>	
CE mark	CE mark	220 to 240 V	
Warranty period	1 years	<b>Line Frequency</b>	
Flammability mark	For mounting on normally flammable surfaces	50 to 60 Hz	
<b>Light Technical</b>		<b>Power Consumption</b>	
Luminous Flux	240 lm	5.8 W	
Correlated Color Temperature (Nom)	3000 K	<b>Power Factor (Fraction)</b>	
Luminous Efficacy (rated) (Nom)	41.38 lm/W	0.4	
Color rendering index (CRI)	>80	<b>Connection</b>	
Number of light sources	96	Screw connection block	
		<b>Cable</b>	
		Cable without plug 2-pole	
		<b>Number of products on MCB of 16 A type B 1</b>	
		<b>Temperature</b>	
		<b>Ambient temperature range</b>	
		-20 to +40 °C	
		<b>Controls and Dimming</b>	
		<b>Dimmable</b>	
		No	

## LED Wall Mount

Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Aluminum and white
Mounting device	Allen screw fixation
Optical cover finish	Matte
Overall length	200 mm
Overall width	200 mm
Overall height	62 mm
Dimensions (Height x Width x Depth)	62 x 200 x 200 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
-------------------------	--

Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	BWS151 LED200/WW PSU 220-240V 9006
Full product name	BWS151 LED200/WW PSU 220-240V 9006
Full product code	911401724401
Order code	911401724401
Material Nr. (12NC)	911401724401
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	24

### Dimensional drawing

