



# UNIUrban

## BGP461 LED40 NW 110-277V TS

UNIUrban is ideal for urban lighting across pathways, parks, gardens, residential areas and shopping centre areas. Its exquisite, stylish yet classic design is not only suitable for modern cities but also for historical architecture.

### Product data

General Information	
Lamp colour code	Neutral white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	PC-MLO [ Polycarbonate micro lens optic]
Connection	Flying leads/wires
Cable	Cable 0.2 m without plug
Protection class IEC	Safety class I (I)
Flammability mark	NO [ -]
CE mark	CE mark
Constant light output	No
LED engine type	LED
Light Technical	
Standard tilt angle post-top	15°
Operating and Electrical	
Input voltage	110 to 277 V
Input frequency	50 to 60 Hz
Power factor (min.)	0.95
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Housing material	Aluminium
Optical cover/lens material	Tempered glass
Mounting device	60S [ Side-entry for diameter 60 mm]
Optical cover/lens finish	Clear
Overall length	691 mm
Overall width	480 mm
Overall height	66 mm
Overall diameter	488 mm
Colour	Grey
Approval and Application	
Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [ 5 J vandal-protected]
Initial Performance (IEC Compliant)	
Initial luminous flux	4000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	120 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	≥70
Initial input power	33 W
Power consumption tolerance	+/-10%


## Application Conditions

Ambient temperature range -40 to +50 °C


## Product Data

Full product code 911401727512  
 Order product name BGP461 LED40 NW 110-277V TS  
 Order code 911401727512  
 Local Code USELED40NWTS

Numerator – quantity per pack 1  
 Numerator – packs per outer box 1  
 Material no. (12NC) 911401727512  
 Net weight (piece) 9.849 kg



## Dimensional drawing



UNIUrban BDP461/BGP461/BSP461/BSS461

