



Flex Cove G4

LS170S LED4 865 IP20 L5000

Flex Cove G4, 400 lm, 105 lm/W, 865 cool daylight, 24 DC V,
Finger-protected

Sustainable and flexible offering with excellent optical performance

Product data

| | | | |
|------------------------------------|-------------------|---|--|
| General Information | | Luminaire light beam spread | |
| Light source replaceable | No | 120° | |
| Number of gear units | - | Operating and Electrical | |
| Driver included | No | Input Voltage | |
| Light source engine type | - | 24 DC V | |
| CE mark | - | Line Frequency | |
| Warranty period | 3 years | - Hz | |
| Flammability mark | - | Initial CLO power consumption | |
| ENEC mark | - | - W | |
| Glow-wire test | - | Average CLO power consumption | |
| EU RoHS compliant | Yes | - W | |
| Light Technical | | Power Consumption | |
| Luminous Flux | 400 lm | 18 W | |
| Correlated Color Temperature (Nom) | 6500 K | Power Factor (Fraction) | |
| Luminous Efficacy (rated) (Nom) | 105 lm/W | 1 | |
| Color rendering index (CRI) | 80 | Connection | |
| Beam angle of light source | 120 degree(s) | Connection unit 2-pole | |
| Light source color | 865 cool daylight | Cable | |
| Optic type | Symmetrical | 2 cables without plug 1-pole | |
| Optical cover type | - | Number of products on MCB of 16 A type B | |
| | | - | |
| | | Temperature | |
| | | Ambient temperature range | |
| | | -20 to +35 °C | |
| | | Controls and Dimming | |
| | | Dimmable | |
| | | No | |
| | | Driver/power unit/transformer | |
| | | - | |
| | | Control interface | |
| | | - | |
| | | Constant light output | |
| | | No | |

Flex Cove G4

| | |
|-------------------------------------|-------------------------|
| Mechanical and Housing | |
| Housing Material | Aluminum |
| Reflector material | - |
| Optic material | - |
| Optical cover material | - |
| Fixation material | - |
| Housing Color | White |
| Optical cover finish | - |
| Overall length | 5,000 mm |
| Overall width | 8 mm |
| Overall height | 1.4 mm |
| Dimensions (Height x Width x Depth) | 1 x 8 x 5000 mm |
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK00 [No protection] |
| Protection class IEC | Safety class III |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |

| | |
|---------------------------------------|----------------------------|
| Initial chromaticity | 0.3102;0.3329; SDCM 4 |
| Power consumption tolerance | +/-10% |
| Over Time Performance (IEC Compliant) | |
| Median useful life L70B50 | 30,000 hour(s) |
| Application Conditions | |
| Maximum dim level | Not applicable |
| Product Data | |
| Order product name | LS170S LED4 865 IP20 L5000 |
| Full product name | LS170S LED4 865 IP20 L5000 |
| Full product code | 911401759422 |
| Order code | 911401759422 |
| Material Nr. (12NC) | 911401759422 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 10 |

Dimensional drawing

