



SmartBright LED Batten G2

BN013C LED20/CW L1200 AU G2

SmartBright LED Batten G2, 20 W, 2000 lm, 6500 K, Wide beam

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

Product data

General Information		Optical cover type	
Light source replaceable	No	Optical cover type	Polycarbonate linear
Number of gear units	1 unit	Luminaire light beam spread	140°
Driver included	Yes	Operating and Electrical	
Light source engine type	LED	Input Voltage	220 to 240 V
CE mark	CE mark	Line Frequency	50 to 60 Hz
Warranty period	3 years	Inrush current	6.75 A
Glow-wire test	Temperature 750 °C, duration 5 s	Inrush time	0.0507 ms
EU RoHS compliant	Yes	Power Consumption	20 W
		Power Factor (Fraction)	0.8
Light Technical		Connection	Flying leads/wires
Luminous Flux	2,000 lm	Cable	Cable without plug 2-pole
Correlated Color Temperature (Nom)	6500 K	Number of products on MCB of 16 A type B	10
Luminous Efficacy (rated) (Nom)	100 lm/W	Temperature	
Color rendering index (CRI)	>80	Ambient temperature range	+20 to +35 °C
Light source color	Cool white		
Optic type	Wide beam		

SmartBright LED Batten G2

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Polyamide
Optic material	Polycarbonate
Optical cover material	Polyamide
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,200 mm
Overall width	30 mm
Overall height	37 mm
Dimensions (Height x Width x Depth)	37 x 30 x 1200 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	SDCM<6
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	25,000 h
---------------------------	----------

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	BN013C LED20/CW L1200 AU G2
Full product name	BN013C LED20/CW L1200 AU G2
Full product code	911401809297
Order code	911401809297
Material Nr. (12NC)	911401809297
Local order code	SB22KLMCW4FTC
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163308289
Numerator - Packs per outer box	12
EAN/UPC - Case	8710163308586

Dimensional drawing

