



SmartBright LED Batten G2

BN013C LED10/CW L600 AU G2

SmartBright LED Batten G2, 10 W, 1000 lm, 6500 K, Wide beam

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

Product data

General Information		Optical cover type		Polycarbonate linear
Light source replaceable	No	Luminaire light beam spread		140°
Number of gear units	1 unit			
Driver included	Yes	Operating and Electrical		
Light source engine type	LED	Input Voltage		220 to 240 V
CE mark	CE mark	Line Frequency		50 to 60 Hz
Warranty period	3 years	Inrush current		6.23 A
Glow-wire test	Temperature 750 °C, duration 5 s	Inrush time		0.0442 ms
EU RoHS compliant	Yes	Power Consumption		10 W
		Power Factor (Fraction)		0.8
Light Technical		Connection		Flying leads/wires
Luminous Flux	1,000 lm	Cable		Cable without plug 2-pole
Correlated Color Temperature (Nom)	6500 K	Number of products on MCB of 16 A type B		10
Luminous Efficacy (rated) (Nom)	100 lm/W			
Color rendering index (CRI)	>80	Temperature		
Light source color	Cool white	Ambient temperature range		+20 to +35 °C
Optic type	Wide beam			

SmartBright LED Batten G2

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Polyamide
Optic material	Polycarbonate
Optical cover material	Polyamide
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	600 mm
Overall width	30 mm
Overall height	37 mm
Dimensions (Height x Width x Depth)	37 x 30 x 600 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Initial chromaticity	SDCM<6
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L70B50	25,000 h

Application Conditions	
Maximum dim level	Not applicable

Product Data	
Order product name	BN013C LED10/CW L600 AU G2
Full product name	BN013C LED10/CW L600 AU G2
Full product code	911401809597
Order code	911401809597
Material Nr. (12NC)	911401809597
Local order code	SB21KLMCW2FTC
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163308319
Numerator - Packs per outer box	12
EAN/UPC - Case	8710163308616

Dimensional drawing

