



# Essential Smartbright LED Batten

## BN068C LED3/CW L300 G2

Essential Smartbright LED Batten, 3.4 W, 300 lm, 6500 K, Wide beam

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

### Product data

General Information		Optic type	
Light source replaceable	No	Wide beam	
Number of gear units	1 unit	Optical cover type	
Driver included	Yes	Polycarbonate linear	
Light source engine type	LED	Luminaire light beam spread	
CE mark	-	140°	
Warranty period	1 years		
Glow-wire test	Temperature 850 °C, duration 5 s		
EU RoHS compliant	Yes		
Light Technical		Operating and Electrical	
Luminous Flux	300 lm	Input Voltage	
Correlated Color Temperature (Nom)	6500 K	220 to 240 V	
Luminous Efficacy (rated) (Nom)	88 lm/W	Line Frequency	
Color rendering index (CRI)	>80	50 to 60 Hz	
Light source color	Cool white	Power Consumption	
		3.4 W	
		Power Factor (Fraction)	
		0.5	
		Connection	
		Flying leads/wires	
		Cable	
		Cable without plug 2-pole	
		Number of products on MCB of 16 A type B	
		10	
		Temperature	
		Ambient temperature range	
		-20 to +40 °C	

# Essential Smartbright LED Batten

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Polyamide
Optic material	Polycarbonate
Optical cover material	Polyamide
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	325 mm
Overall width	21 mm
Overall height	34.2 mm
Dimensions (Height x Width x Depth)	34 x 21 x 325 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L70B50	20,000 hour(s)

Application Conditions	
Maximum dim level	Not applicable

Product Data	
Order product name	BN068C LED3/CW L300 G2
Full product name	BN068C LED3/CW L300 G2
Full product code	911401818497
Order code	01818497
Material Nr. (12NC)	911401818497
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163310381
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163310688

## Dimensional drawing

