



Essential Smartbright LED Batten

BN068C LED12/WW L1200 G2

Essential Smartbright LED Batten, 13 W, 1200 lm, 3000 K, Wide beam

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

Product data

General Information		Optic type	
Light source replaceable	No	Wide beam	
Number of gear units	1 unit	Optical cover type	Polycarbonate linear
Driver included	Yes	Luminaire light beam spread	140°
Light source engine type	LED	Operating and Electrical	
CE mark	-	Input Voltage	220 to 240 V
Warranty period	1 years	Line Frequency	50 to 60 Hz
Glow-wire test	Temperature 850 °C, duration 5 s	Power Consumption	13 W
EU RoHS compliant	Yes	Power Factor (Fraction)	0.5
Light Technical		Connection	Flying leads/wires
Luminous Flux	1,200 lm	Cable	Cable without plug 2-pole
Correlated Color Temperature (Nom)	3000 K	Number of products on MCB of 16 A type B	10
Luminous Efficacy (rated) (Nom)	92 lm/W	Temperature	
Color rendering index (CRI)	>80	Ambient temperature range	-20 to +40 °C
Light source color	Warm white		

Essential Smartbright LED Batten

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing	
Housing Material	Polyamide
Optic material	Polycarbonate
Optical cover material	Polyamide
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,185 mm
Overall width	21 mm
Overall height	34.2 mm
Dimensions (Height x Width x Depth)	34 x 21 x 1185 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L70B50	20,000 hour(s)

Application Conditions	
Maximum dim level	Not applicable

Product Data	
Order product name	BN068C LED12/WW L1200 G2
Full product name	BN068C LED12/WW L1200 G2
Full product code	911401819597
Order code	01819597
Material Nr. (12NC)	911401819597
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163310497
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163310794

Dimensional drawing

