



Essential Smartbright LED Batten

BN068C LED3/NW L300 TH G2

Essential Smartbright LED Batten, 3.4 W, 300 lm, 4000 K, Wide beam

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. This new batten range of LED products can be used to replace traditional battens with fluorescent lamps. The process of selecting, installing and maintaining is so easy – it's a simple switch

Product data

General Information		Optic type	
Light source replaceable	No	Wide beam	
Number of gear units	1 unit	Optical cover type	Polycarbonate linear
Driver included	Yes	Luminaire light beam spread	140°
Light source engine type	LED	Operating and Electrical	
CE mark	-	Input Voltage	220 to 240 V
Warranty period	1 years	Line Frequency	50 to 60 Hz
Glow-wire test	Temperature 850 °C, duration 5 s	Power Consumption	3.4 W
EU RoHS compliant	Yes	Power Factor (Fraction)	0.5
Light Technical		Connection	Flying leads/wires
Luminous Flux	300 lm	Cable	Cable without plug 2-pole
Correlated Color Temperature (Nom)	4000 K	Number of products on MCB of 16 A type B	10
Luminous Efficacy (rated) (Nom)	88 lm/W	Temperature	
Color rendering index (CRI)	>80	Ambient temperature range	-20 to +40 °C
Light source color	Neutral white		

Essential Smartbright LED Batten

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Polyamide
Optic material	Polycarbonate
Optical cover material	Polyamide
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	325 mm
Overall width	21 mm
Overall height	34.2 mm
Dimensions (Height x Width x Depth)	34 x 21 x 325 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK00 [No protection]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<7
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	20,000 hour(s)
---------------------------	----------------

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	BN068C LED3/NW L300 TH G2
Full product name	BN068C LED3/NW L300 TH G2
Full product code	911401820397
Order code	01820397
Material Nr. (12NC)	911401820397
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163310572
Numerator - Packs per outer box	24
EAN/UPC - Case	8710163310879

Dimensional drawing

