

PHILIPS

Lighting



Smartbright CCT/ Wattage Tunable Waterproof batten

WT067C SWT SCCT LED L600 PSU AU

The new SmartBright Tri Colour Waterproof Batten provides flexibility the customer to choose from 3 colour temperatures and 2 wattages before installation, to suit specific needs.

Product data

General Information		Number of products on MCB	
Beam angle of light source	120 °	Number of products on MCB	38
Lamp colour code	White	RoHS mark	-
Light source replaceable	No	Operating and Electrical	
Number of gear units	1 unit	Input voltage	220 to 240 V
Driver/power unit/transformer	PSU [Power supply unit]	Input frequency	50 or 60 Hz
Driver included	Yes	Inrush current	8.88 A
Optic type	120 [Beam angle 120°]	Inrush time	0.04 ms
Optical cover/lens type	PC [Polycarbonate bowl/cover]	Power factor (min.)	0.9
Luminaire light beam spread	120°	Controls and Dimming	
Connection	CU3 [Connection unit 3-pole]	Dimmable	No
Cable	-	Mechanical and Housing	
Protection class IEC	Safety class I (I)	Housing material	Polycarbonate
Glow-wire test	650/30 [Temperature 650 °C, duration 30 s]	Reflector material	Steel
Flammability mark	NO [-]	Optic material	Polycarbonate
CE mark	-	Optical cover/lens material	Polycarbonate
ENEC mark	-	Fixation material	-
Warranty period	5 years		
Constant light output	No		

Smartbright CCT/Wattage Tunable Waterproof batten

Optical cover/lens finish	Opal
Overall length	656 mm
Overall width	107 mm
Overall height	72 mm
Colour	Grey

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)

Initial luminous flux	2000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	100 lm/W
Lamp colour temperature	- K
Colour Rendering Index	>80
Initial chromaticity	0.38;0.38
Initial input power	20 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	72000 h
---------------------------	---------


Median useful life L80B50	44000 h
Median useful life L90B50	21000 h

Application Conditions

Ambient temperature range	-20 to +40 °C
Maximum dimming level	Not applicable

Product Data

Full product code	871016334430099
Order product name	WT067C SWT SCCT LED L600 PSU AU
EAN/UPC – product	8710163344300
Order code	911401821680
Numerator – quantity per pack	1
Numerator – packs per outer box	9
Material no. (12NC)	911401821680
Net weight (piece)	1.010 kg



Dimensional drawing



WT066C/WT067C

