

Greenperform Waterproof G2 - WT188C

WT188C LED10 NW L600 PSU TW

Greenperform Waterproof G2 - WT188C, 9 W, 1000 lm, 4000 K, 120°

Greenperform Waterproof G2 luminaire and its components are designed for both indoor and semi-outdoor application (anti-UV PC material housing and diffuser, stainless steel installation accessory). We design for friendly optical, energy saving, reliable quality, and easy wiring. Beyond that, GreenParking wireless motion detective system is ready to provide the maximum energy saving and new lighting experience to you.

Product data

| General Information | |
|--------------------------|----------------------------------|
| Light source replaceable | No |
| Number of gear units | 1 unit |
| Driver included | Yes |
| Light source engine type | LED |
| CE mark | CE mark |
| Warranty period | 3 years |
| Flammability mark | - |
| ENEC mark | - |
| Glow-wire test | Temperature 750 °C, duration 5 s |
| EU RoHS compliant | Yes |

| Light Technical | |
|------------------------------------|--------------------------------|
| Luminous Flux | 1,000 lm |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 110 lm/W |
| Color rendering index (CRI) | >80 |
| Beam angle of light source | - degree(s) |
| Light source color | Neutral white |
| Optic type | Symmetrical |
| Optical cover type | Polycarbonate bowl/cover foggy |
| Luminaire light beam spread | 120° |

Greenperform Waterproof G2 - WT188C

Operating and Electrical

| | |
|--|--------------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Inrush current | 14 A |
| Inrush time | 0.25 ms |
| Power Consumption | 9 W |
| Power Factor (Fraction) | 0.9 |
| Connection | Floating connector |
| Number of products on MCB of 16 A type B | 24 |

Temperature

| | |
|---------------------------|---------------|
| Ambient temperature range | -30 to +45 °C |
|---------------------------|---------------|

Controls and Dimming

| | |
|-------------------------------|----------------------------|
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Control interface | - |
| Constant light output | No |

Mechanical and Housing

| | |
|------------------------|-----------------|
| Housing Material | Polycarbonate |
| Reflector material | Steel |
| Optic material | Polycarbonate |
| Optical cover material | Polycarbonate |
| Fixation material | Stainless steel |
| Housing Color | Gray and white |
| Optical cover finish | Opal |
| Overall length | 615 mm |
| Overall width | 84 mm |
| Overall height | 83 mm |

| | |
|-------------------------------------|------------------|
| Dimensions (Height x Width x Depth) | 83 x 84 x 615 mm |
|-------------------------------------|------------------|

Approval and Application

| | |
|------------------------------|--|
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK08 [5 J vandal-protected] |
| Protection class IEC | Safety class I |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | SDCM<5 |
| Power consumption tolerance | +/-10% |

Over Time Performance (IEC Compliant)

| | |
|---------------------------|----------|
| Median useful life L70B50 | 50,000 h |
| Median useful life L80B50 | 45,000 h |
| Median useful life L90B50 | 35,000 h |


Application Conditions

| | |
|-------------------|----------------|
| Maximum dim level | Not applicable |
|-------------------|----------------|

Product Data

| | |
|---------------------------------|-----------------------------|
| Order product name | WT188C LED10 NW L600 PSU TW |
| Full product name | WT188C LED10 NW L600 PSU TW |
| Full product code | 911401830597 |
| Order code | 911401830597 |
| Material Nr. (12NC) | 911401830597 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |

Dimensional drawing



Greenperform Waterproof G2 – WT188C

