



Greenperform Waterproof G2 - WT188C

WT188C LED20 NW L1200 PSU TB

Greenperform Waterproof G2 luminaire and its components are designed for both indoor and semi-outdoor application (anti-UV PC material housing and diffuser, stainless steel installation accessory). We design for friendly optical, energy saving, reliable quality, and easy wiring.;Beyond that, GreenParking wireless motion detective system is ready to provide the maximum energy saving and new lighting experience to you.

Product data

General Information		Warranty period	
Beam angle of light source	- °	Warranty period	3 years
Lamp colour code	Neutral white	Constant light output	No
Light source replaceable	No	Number of products on MCB	24
Number of gear units	1 unit	RoHS mark	RoHS mark
Driver/power unit/transformer	PSU [Power supply unit]	Operating and Electrical	
Driver included	Yes	Input voltage	220 to 240 V
Optic type	Symmetrical	Input frequency	50 to 60 Hz
Luminaire light beam spread	120°	Inrush current	4 A
Control interface	-	Inrush time	0.058 ms
Connection	Screw connection block	Power factor (min.)	0.9
Protection class IEC	Safety class I (I)	Controls and Dimming	
Glow-wire test	750/5 [Temperature 750 °C, duration 5 s]	Dimmable	No
Flammability mark	NO [-]		
CE mark	CE mark		
ENEC mark	-		

Greenperform Waterproof G2 - WT188C

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Optical cover/lens finish	Opal
Overall length	1183 mm
Overall width	84 mm
Overall height	83 mm
Colour	Grey and White

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)

Initial luminous flux	2000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	125 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	>80
Initial chromaticity	SDCM<5

Initial input power	16 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Median useful life L70B50	50000 h
Median useful life L80B50	45000 h
Median useful life L90B50	35000 h

Application Conditions


Ambient temperature range	-30 to +45 °C
Maximum dimming level	Not applicable

Product Data

Full product code	911401832797
Order product name	WT188C LED20 NW L1200 PSU TB
Order code	911401832797
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911401832797
Net weight (piece)	1.299 kg



Dimensional drawing



WT188C/WL020C

