



Smart Post-top G3

BGP161 LED2500/NW PSU 220-240V 9006 GM

Smart Post-top G3, 2500 lm, 29 W, Neutral white, Symmetrical,
Safety class I, Post-top for diameter 60 mm

Smart Post Top G3 inherits the classic look and style of the previous generation with improved system efficacy and light quality. The Smart Post Top G3 optimized optical design increases both horizontal and vertical uniformity. The highly efficient thermal system design ensures maximum heat transfer and longer LED service life. This reliable luminaire system operates well in both low and high temperature environments. It offers more than 11 years expected life, reducing maintenance frequency and cost (based on a 50,000 hour rated life and 12 hours operation per day). It provides a comfortable and safe atmosphere to gardens, residential areas, courtyards, side streets, squares, parks & playgrounds.

Product data


General Information		Light Technical	
Lamp family code	-	Upward light output ratio	0
Light source replaceable	Yes	Luminous Flux	2500 lm
Number of gear units	1 unit	Standard tilt angle posttop	-
Driver included	Yes	Standard tilt angle side entry	-
Light source engine type	LED	Correlated Color Temperature (Nom)	4000 K
CE mark	-	Luminous Efficacy (rated) (Nom)	86.21 lm/W
Warranty period	3 years	Color rendering index (CRI)	70
Flammability mark	For mounting on normally flammable surfaces	Light source color	Neutral white
ENEC mark	-	Optical cover type	Acrylate cover and semi-matt high-reflective optic
EU RoHS compliant	Yes	Luminaire light beam spread	-
		Optic type outdoor	Symmetrical

Smart Post-top G3

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	2.1 A
Inrush time	22.3 ms
Power Consumption	29 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 0.45 m without plug
Number of products on MCB of 16 A type B -	
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Acrylate
Optic material	Acrylate
Optical cover material	Acrylate
Fixation material	Stainless steel
Housing Color	Gray
Mounting device	Post-top for diameter 60 mm
Optical cover shape	Flat
Optical cover finish	Frosted
Overall height	265 mm

Overall diameter	578 mm
Effective projected area	0.11 m²
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Surge Protection (Common/Differential)	4/2 kV
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM ≤ 5
Power consumption tolerance	+/-10%
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BGP161 LED2500/NW PSU 220-240V 9006 GM
Full product name	BGP161 LED2500/NW PSU 220-240V 9006 GM
Full product code	872016952022699
Order code	911401834798
Material Nr. (12NC)	911401834798
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169520226
Numerator - Packs per outer box	2
EAN/UPC - Case	8720169520226

Dimensional drawing



Smart Post-top G3

