



SmartBright Panel

RC099V LED26S/865 W60L60 PCV GM

SmartBright Panel, 865 cool daylight

SmartBright Panel is the most affordable LED panel delivering comfortable light with excellent uniformity

Product data

General Information		Controls and Dimming	
Light source replaceable	No	Dimmable	No
Number of gear units	1 unit	Driver/power unit/transformer	Power supply unit (On/Off)
Driver included	Yes	Constant light output	Yes
CE mark	CE mark		
ENEC mark	-	Mechanical and Housing	
Glow-wire test	Temperature 650 °C, duration 30 s	Housing Material	Steel
		Reflector material	Steel
		Optic material	Polycarbonate
		Housing Color	White
Light Technical		Approval and Application	
Correlated Color Temperature (Nom)	6500 K	Ingress protection code	IP20 [Finger-protected]
Color rendering index (CRI)	80	Mech. impact protection code	IK02 [0.2 J standard]
Number of light sources	12	Protection class IEC	Safety class I
Light source color	865 cool daylight		
Optic type	Beam angle 60 to 120°	Initial Performance (IEC Compliant)	
Optical cover type	Transparent bowl with white cover	Luminous flux tolerance	+/-10%
Luminaire light beam spread	110° x 110°	Power consumption tolerance	+/-10%
Operating and Electrical		Product Data	
Input Voltage	220-240 V	Order product name	RC099V LED26S/865 W60L60 PCV GM
Power Factor (Fraction)	0.9		



SmartBright Panel

Full product name	RC099V LED26S/865 W60L60 PCV GM
Full product code	911401834899
Order code	911401834899
Material Nr. (12NC)	911401834899

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

Product Type	Size LxWxH(mm)
RC099V LED26S W60x60 GH	597x297x15
RC099V LED26S W60x120 GH	1197x297x15
RC099V LED26S W60x60 SUS GH	603x603x15
RC099V LED26S W60x120 SUS GH	1203x603x15
RC099V LED26S W60x60 PCV GH	603x603x15
RC099V LED26S W60x120 PCV GH	1203x603x15
RC099V LED26S W60x60 GH	597x297x15
RC099V LED26S W60x120 GH	1197x297x15
RC099V LED26S W60x60 SUS GH	603x603x15
RC099V LED26S W60x120 SUS GH	1203x603x15
RC099V LED26S W60x60 PCV GH	603x603x15
RC099V LED26S W60x120 PCV GH	1203x603x15



RC099V LED26S W60x60 GH
 RC099V LED26S W60x120 SUS GH
 RC099V LED26S W60x60 PCV GH
 RC099V LED26S W60x120 GH
 RC099V LED26S W60x60 GH
 RC099V LED26S W60x120 GH
 RC099V LED26S W60x60 SUS GH
 RC099V LED26S W60x120 SUS GH
 RC099V LED26S W60x60 PCV GH
 RC099V LED26S W60x120 PCV GH

