



SmartBright Panel

RC099V LED36S/840 W60L60 GM

SmartBright Panel, 840 neutral white

SmartBright Panel is the most affordable LED panel delivering comfortable light with excellent uniformity

Product data



General Information		Controls and Dimming	
Light source replaceable	No	Dimmable	No
Number of gear units	1 unit	Driver/power unit/transformer	Power supply unit (On/Off)
Driver included	Yes	Constant light output	Yes
CE mark	CE mark		
ENEC mark	-	Mechanical and Housing	
Glow-wire test	Temperature 650 °C, duration 30 s	Housing Material	Steel
		Reflector material	Steel
Light Technical		Optic material	Polycarbonate
Correlated Color Temperature (Nom)	4000 K	Housing Color	White
Color rendering index (CRI)	80		
Number of light sources	12	Approval and Application	
Light source color	840 neutral white	Ingress protection code	IP20 [Finger-protected]
Optic type	Beam angle 60 to 120°	Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Transparent bowl with white cover	Protection class IEC	Safety class I
Luminaire light beam spread	110° x 110°		
		Initial Performance (IEC Compliant)	
Operating and Electrical		Luminous flux tolerance	+/-10%
Input Voltage	220-240 V	Power consumption tolerance	+/-10%
Power Consumption	34 W		
Power Factor (Fraction)	0.9	Product Data	
		Order product name	RC099V LED36S/840 W60L60 GM

Full product name	RC099V LED36S/840 W60L60 GM
Full product code	911401835199
Order code	911401835199
Material Nr. (12NC)	911401835199

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

Product Type	Size LxWxH(mm)
RC099V LED36S W60x60 GM	597x297x75
RC099V LED36S W60x120 GM	1197x297x75
RC099V LED36S W60x60 SLS GM	603x603x75
RC099V LED36S W60x120 SLS GM	1203x603x75
RC099V LED36S W60x60 PCV GM	603x603x75
RC099V LED36S W60x120 PCV GM	1203x603x75
RC099V LED36S W60x60 SLS GM	597x297x75
RC099V LED36S W60x120 SLS GM	1197x297x75
RC099V LED36S W60x60 SLS GM	603x603x75
RC099V LED36S W60x120 SLS GM	1203x603x75
RC099V LED36S W60x60 PCV GM	603x603x75
RC099V LED36S W60x120 PCV GM	1203x603x75



RC099V LED36S W60x60 GM
RC099V LED36S W60x120 SLS GM
RC099V LED36S W60x60 PCV GM
RC099V LED36S W60x120 SLS GM
RC099V LED36S W60x60 PCV GM

RC099V LED36S W60x120 GM
RC099V LED36S W60x120 SLS GM
RC099V LED36S W60x120 PCV GM
RC099V LED36S W60x120 SLS GM
RC099V LED36S W60x120 PCV GM

