



SmartBright LED Batten

BN012C LED20/CW L1200

SmartBright LED Batten G2 is an affordable replacement for T5 and T8 batten in indirect lighting solutions, such as pelmet or cove lighting. The product comes in a variety of lengths, and an excellent lifetime of 30,000 hours. The product also comes with a plug in the packaging, so is easy for installation.

Product data

General Information	
Light source replaceable	No
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Optic type	No [-]
Luminaire light beam spread	110°
Flammability mark	NO [-]
CE mark	CE mark
ENEC mark	-
UL mark	-

Operating and Electrical	
Input voltage	220-240 V
Input frequency	50 to 60 Hz
Power factor (nom.)	0.8

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Housing material	Polycarbonate
Optic material	Polycarbonate
Colour	White

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Init. Corr. colour temperature	6500 K
Init. colour rendering index	80
Initial input power	21 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Median useful life L70B50	30000 h

SmartBright LED Batten

Application Conditions


Ambient temperature range	-20 to +35 °C
Maximum dimming level	Not applicable

Product Data

Full product code	911401840299
Order product name	BN012C LED20/CW L1200
EAN/UPC – product	8710163301259

Order code	01840299
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	911401840299
Net weight (piece)	0.240 kg

Dimensional drawing



SmartBright LED Batten BN012C

