



# GreenUp Lowbay G2

## BY288P LED40/NW PSU EN

Neutral white - Power supply unit

Good lighting is essential in industrial workspaces and large indoor areas. The wrong choice of lights or a lighting not correctly planned can lead to eye strain, fatigue, and poor performance, compromising safety and productivity. The Philips GreenUp Lowbay G2 luminaire is a simple LED solution which efficiently illuminates work areas, creating a brighter and better work, retail or sporting environment. With its crisp, white light and high colour rendering index coupled with energy efficiency, high visibility and enhances safety 24/7. Equipped with motion detection function, this easy-to-install and low-maintenance lighting solution is suitable for a variety of applications.

### Product data

General Information		Operating and Electrical	
Lamp colour code	Neutral white	Constant light output	No
Light source replaceable	No	Number of products on MCB	24
Number of gear units	1 unit	RoHS mark	-
Driver/power unit/transformer	PSU [ Power supply unit]	Operating and Electrical	
Driver included	Yes	Input voltage	220-400 V
Optic type	No [-]	Input frequency	50 or 60 Hz
Luminaire light beam spread	96°	Inrush current	14.8 A
Connection	Flying leads/wires	Inrush time	0.0025 ms
Cable	Cable 0.3 m without plug	Power factor (min.)	0.95
Protection class IEC	Safety class I (I)	Controls and Dimming	
Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]	Dimmable	no
Flammability mark	F [ For mounting on normally flammable surfaces]	Mechanical and Housing	
CE mark	CE mark	Housing material	Aluminum die-cast
ENEC mark	-		
Warranty period	3 years		

## GreenUp Lowbay G2

Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Frosted
Overall height	115 mm
Overall diameter	150 mm
Colour	Grey

### Approval and Application

Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK03 [ 0.3 J]

### Initial Performance (IEC Compliant)

Initial luminous flux	3600 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	120 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	>80
Initial chromaticity	(0.38.0.38)SDCM<5
Initial input power	30 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)


Median useful life L70B50	50000 h
Median useful life L80B50	40000 h
Median useful life L90B50	20000 h

### Application Conditions


Ambient temperature range	-20 to +45 °C
Suitable for random switching	No

### Product Data

Full product code	911401843199
Order product name	BY288P LED40/NW PSU EN
Order code	911401843199
Local Code	BY288P40W4KF
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911401843199
Net weight (piece)	1.200 kg



### Dimensional drawing



BY288P/BY288X GreenUp Lowbay G2

