



# GreenUp Lowbay G2

## BY288P LED60/CW PSU EN

GreenUp Lowbay G2, 50 W, 5900 lm, 6500 K, 102°

Good lighting is essential in industrial workspaces and large indoor areas. The wrong choice of lights or a lighting not correctly planned can lead to eye strain, fatigue, and poor performance, compromising safety and productivity. The Philips GreenUp Lowbay G2 luminaire is a simple LED solution which efficiently illuminates work areas, creating a brighter and better work, retail or sporting environment. With its crisp, white light and high color rendering index coupled with energy efficiency, high visibility and enhances safety 24/7. Equipped with motion detection function, this easy-to-install and low-maintenance lighting solution is suitable for a variety of applications.

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Service tag	Yes
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	No
Light Technical	
Luminous Flux	5900 lm

Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	118 lm/W
Color rendering index (CRI)	<gt;/>80
Light source color	Cool white
Optic type	-
Optical cover type	Opal
Luminaire light beam spread	102°
Operating and Electrical	
Input Voltage	220-400 V
Line Frequency	50 or 60 Hz
Inrush current	3.5 A
Inrush time	0.05 ms
Power Consumption	50 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires

## GreenUp Lowbay G2

Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B	24

### Temperature

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	Grey
Optical cover finish	Frosted
Overall height	144 mm
Overall diameter	250 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]

Protection class IEC	Safety class I
----------------------	----------------

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.313.0.324)SDCM<lt/>5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.01 %
Median useful life L70B50	50000 hour(s)
Median useful life L80B50	40000 hour(s)
Median useful life L90B50	20000 hour(s)


### Application Conditions

Suitable for random switching	No
-------------------------------	----

### Product Data

Order product name	BY288P LED60/CW PSU EN
Full product name	BY288P LED60/CW PSU EN
Full product code	911401843399
Order code	911401843399
Material Nr. (12NC)	911401843399
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing



## GreenUp Lowbay G2

